


# Intel Core i5 13600K - 3.5 GHz - 14 Kerne - 20 Threads

24 MB Cache-Speicher - FCLGA1700 Socket - Box

Gruppe	Prozessoren
Hersteller	Intel
Hersteller Art. Nr.	BX8071513600K
EAN/UPC	5032037258746



## Beschreibung

Intel Core i5 13600K - 3.5 GHz - 14 Kerne - 20 Threads - 24 MB Cache-Speicher - FCLGA1700 Socket - Box

## Hauptmerkmale

Produktbeschreibung	Intel Core i5 13600K / 3.5 GHz Prozessor - Box
Produkttyp	Prozessor
Prozessortyp	Intel Core i5 13600K (13th Gen)
Anz. der Kerne	14 Kerne / 20 Threads
Cache-Speicher	24 MB
Integrierte Grafik	Intel UHD Graphics 770
Geeignete Sockel	FCLGA1700 Socket
Prozessoranz.	1
Taktfrequenz	3.5 GHz (P-Kern) / 2.6 GHz (E-Kern)
Max. Turbo-Taktfrequenz	5.1 GHz (P-Kern) / 3.9 GHz (E-Kern)
Herstellungsprozess	10 nm
Funktionen	Enhanced SpeedStep technology, Hyper-Threading-Technologie, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Intel Trusted Execution Technology, Streaming-SIMD-Erweiterungen 4.1, Streaming-SIMD-Erweiterungen 4.2, Intel Turbo Boost Technology 2.0, Intel AES New Instructions (AES-NI), Thermal Monitoring Technologies, Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Secure Key, Intel Advanced Vector Extensions 2 (AVX2.0), Intel OS Guard, Intel Speed Shift Technology, Mode-based Execute Control (MBE), Intel Volume Management Device (VMD), Intel Boot Guard, Intel Deep Learning Boost (DL Boost), Intel Control-Flow Enforcement Technology, Intel Gaussian and Neural Accelerator 3.0, Intel Thread Director, Instruction Set 64-bit, Intel Stable IT Platform Program (SIPP), Intel Standard Manageability (ISM), Intel Virtualization Technology with Redirect Protection (VT-rp)

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.