

Samsung Galaxy S25 Smartphone AI, Display 6.2" FHD+ Dynamic AMOLED 2X, Fotocamera 50MP, RAM 12GB, 128GB, 4.000 mAh, Mint



Galaxy S25
Galaxy AI



Marchio : Samsung

Famiglia del prodotto: Galaxy

Codice prodotto: SM-S931BLGDEUE

Nome del prodotto : Samsung Galaxy S25 Smartphone AI, Display 6.2" FHD+ Dynamic AMOLED 2X, Fotocamera 50MP, RAM 12GB, 128GB, 4.000 mAh, Mint

- Galaxy AI. Un concentrato di intelligenza al tuo servizio
- ProVisual Engine di ultima generazione. Immagini naturali in tutte le condizioni di illuminazione
- Un processore potentissimo realizzato appositamente per i dispositivi Galaxy S25


Samsung Galaxy S25 Smartphone AI, Display 6.2" FHD+ Dynamic AMOLED 2X, Fotocamera 50MP, RAM 12GB, 128GB, 4.000 mAh, Mint:

SM-S931BLGDEUE

Samsung Galaxy S25 Smartphone AI, Display 6.2" FHD+ Dynamic AMOLED 2X, Fotocamera 50MP, RAM 12GB, 128GB, 4.000 mAh, Mint. Dimensioni diagonale schermo: 15,8 cm (6.2"), Risoluzione del display: 2340 x 1080 Pixel. Famiglia processore: Qualcomm Snapdragon, Modello del processore: 8 Elite. Capacità della RAM: 12 GB, Capacità memoria interna: 128 GB. Risoluzione fotocamera posteriore (numerico): 50 MP, Tipo di fotocamera posteriore: Tripla fotocamera. Capacità della scheda SIM: Doppia SIM. Sistema operativo incluso: Android 15. Capacità della batteria: 4000 mAh. Colore del prodotto: Colore menta. Peso: 162 g

Display		Camera	
Display diagonal *	15.8 cm (6.2")	Panorama	✓
Screen shape	Flat	Portrait mode	✓
Display technology marketing name	Dynamic AMOLED 2X	Slow motion mode	✓
Panel type	AMOLED	Slow motion rate	240fps in FHD, 120fps in FHD, 120fps in UHD
Display glass type	Gorilla Glass	Camera image formats supported	DNG, HEIF, JPEG
Gorilla Glass version	Gorilla Glass Victus 2	Network	
Display resolution *	2340 x 1080 pixels	SIM card capability *	Dual SIM
Display number of colours	16 million colours	Mobile network generation *	5G
Maximum refresh rate	120 Hz	SIM card type *	NanoSIM + eSIM
Display brightness	1500 cd/m ²	3G standards *	UMTS, WCDMA
Pixel density	418 ppi	4G standard *	LTE-TDD & LTE-FDD
Brand specific technologies	Always-on display	5G standard *	Sub6 FDD, Sub6 SDL, Sub6 TDD
Rounded display corners	✓	Wi-Fi	✓
Processor		Top Wi-Fi standard *	Wi-Fi 7 (802.11be)
Processor family *	Qualcomm Snapdragon	Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n), Wi-Fi 5 (802.11ac), Wi-Fi 6 (802.11ax), Wi-Fi 6E (802.11ax), Wi-Fi 7 (802.11be)
Processor model *	8 Elite	Bluetooth *	✓
Processor cores	8	Bluetooth version	5.4
Processor boost frequency	4.47 GHz	3G bands supported	850,900,1900,2100 MHz
Artificial Intelligence processor family	Qualcomm	4G bands supported	700,800,850,900,1500,1800,1900,2100,2300,2500,2600 MHz
Storage		5G bands supported	700,800,850,900,1500,1800,1900,2100,2300,2500,2600,3500,3700 MHz
RAM capacity *	12 GB	4G data rate (max)	2000 Mbit/s
Internal storage capacity *	128 GB	5G data rate (max)	4.66 Gbit/s
Compatible memory cards *	Not supported	Wi-Fi Direct	✓
Camera		MIMO	✓
Rear camera sensor size	1/1.56"	Modulation	4096-QAM
Second rear camera sensor size	1/3.94"	Near Field Communication (NFC)	✓
Third rear camera sensor size	1/2.55"	Ports & interfaces	
		USB port	✓
		USB connector type	USB Type-C
		Headphone connectivity	USB Type-C

Camera		Design	
Rear camera resolution (numeric) *	50 MP	Form factor *	Bar
Second rear camera resolution (numeric)	10 MP	Product colour *	Mint colour
Third rear camera resolution (numeric)	12 MP	International Protection (IP) code	IP68
Rear camera aperture number	1.8	Performance	
Second rear camera aperture number	2.4	Fast charging	✓
Third rear camera aperture number	2.2	Wireless charging	✓
Rear camera pixel size	1 µm	Fingerprint reader	✓
Rear camera pixel size (Quad Pixel technology)	1 µm	Face recognition	✓
Second rear camera pixel size	1.4 µm	Navigation	
Rear camera field of view (FOV) angle	85°	GPS (satellite)	✓
Second rear camera field of view (FOV) angle	36°	GLONASS	✓
Third rear camera field of view (FOV) angle	120°	BeiDou	✓
Optical zoom	3x	Galileo	✓
Digital zoom	30x	Quasi-Zenith Satellite System (QZSS)	✓
Front camera type *	Single camera	Position location *	✓
Front camera sensor size	1/3.2"	Multimedia	
Front camera resolution (numeric) *	12 MP	Audio formats supported	3GA, AAC, AMR, APE, AWB, DFF, DSF, FLAC, IMY, M4A, Mid, MIDI, MP3, MXMF, OGA, OGG, OTA, RTTTL, RTX, WAV, XMF
Front camera aperture number	2.2	Video formats supported	3G2, 3GP, AVI, FLV, MKV, MP4, WEBM
Front camera pixel size	1.12 µm	Software	
Front camera field of view (FOV) angle	80°	Platform *	Android
Rear camera flash *	✓	Operating system installed *	Android 15
Flash type	LED	Operating system fork	One UI 7.0
Video capture resolution (max)	4320 x 7680 pixels	Battery	
Maximum frame rate	240 fps	Battery capacity *	4000 mAh
Resolution at capture speed	1280x720@30fps, 1920x1080@30fps, 1920x1080@60fps, 3840x2160@30fps, 3840x2160@60fps	Sensors	
Video recording modes	720p, 1080p, 2160p, 4320p	Proximity sensor	✓
Rear camera type *	Triple camera	Accelerometer	✓
Auto focus	✓	Ambient light sensor	✓
Image stabilizer	✓	Gyroscope	✓
Image stabilizer type	Optical Image Stabilization (OIS)	Barometer	✓
Night mode	✓	Geomagnetic sensor	✓
		Hall sensor	✓
		Power	
		USB Type-C charging port	✓
		Weight & dimensions	
		Width	70.5 mm
		Depth	7.2 mm
		Height	146.9 mm
		Weight *	162 g
		Packaging content	
		AC adapter included *	✗



8806095852881

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 10-MAR-2025. Prints or copies of Information are only valid on the printed Publication date