

U.I. Lapp GmbH - REACH / RoHS Substance Information



Date: 02.04.2025

Article Information		REACH - SVHC (June 27th 2024)		RoHS (2011/65/EU - (EU) 2015/863)			
Material part number	Designation	Contains the product a SVHC above 0,1 %?	Name of SVHC	RoHS restricted substances contained exceeding limit values?	Exemption used?	Number of exemption	Description
0012453	ÖLFLEX 540 P 3G0,75	No	-	No	No	-	-
0012463	ÖLFLEX 540 P 3G1,5	No	-	No	No	-	-
0013621	H07BQ-F 3G1,5	No	-	No	No	-	-
0023114	ÖLFLEX SOLAR XLS-R 1X6 RD/BK	No	-	No	No	-	-
0023137	ÖLFLEX SOLAR XLS-R 1X4 WH/BK	No	-	No	No	-	-
0023138	ÖLFLEX SOLAR XLS-R 1X6 WH/BK	No	-	No	No	-	-
0023142	ÖLFLEX SOLAR XLS-R 1X4 RD/BK	No	-	No	No	-	-
0028202	UNITRONIC LiYY 2x0,14	No	-	No	No	-	-
0028204	UNITRONIC LiYY 4x0,14	No	-	No	No	-	-
0028207	UNITRONIC LiYY 7x0,14	No	-	No	No	-	-
0028404	UNITRONIC LiYY 4x0,34	No	-	No	No	-	-
0034302	UNITRONIC LiYCY 2x0,14	No	-	No	No	-	-
0034304	UNITRONIC LiYCY 4x0,14	No	-	No	No	-	-
0034306	UNITRONIC LiYCY 6x0,14	No	-	No	No	-	-
0034308	UNITRONIC LiYCY 8x0,14	No	-	No	No	-	-
0034310	UNITRONIC LiYCY 10x0,14	No	-	No	No	-	-
0034325	UNITRONIC LiYCY 25x0,14	No	-	No	No	-	-
0035131	UNITRONIC LiYCY (TP) 2x2x0,14	No	-	No	No	-	-
0035133	UNITRONIC LiYCY (TP) 6x2x0,14	No	-	No	No	-	-
0046014	ÖLFLEX HEAT 180 SiHF 3G1,5	No	-	No	No	-	-
1119003	ÖLFLEX CLASSIC 110 3G0,5	No	-	No	No	-	-
1119405	ÖLFLEX CLASSIC 110 5G2,5	No	-	No	No	-	-
1119752	ÖLFLEX CLASSIC 110 2X0,5	No	-	No	No	-	-
1120233	ÖLFLEX CLASSIC 110 Black 0,6/1kV 3G0,75	No	-	No	No	-	-
1120267	ÖLFLEX CLASSIC 110 Black 0,6/1kV 3G1	No	-	No	No	-	-
1120307	ÖLFLEX CLASSIC 110 Black 0,6/1kV 3G1,5	No	-	No	No	-	-
1135303	ÖLFLEX CLASSIC 110 CY 3G1,5	No	-	No	No	-	-
1312304	ÖLFLEX CLASSIC 400 P 4G1,5	No	-	No	No	-	-
15500013	NYI-J 3x1,5 RE 0,6/1kV	No	-	No	No	-	-
15500033	NYI-J 5x1,5 RE 0,6/1kV	No	-	No	No	-	-
15500123	NYI-J 5x2,5 RE 0,6/1kV	No	-	No	No	-	-
1591301	J-Y(ST)Y...LG 2x2x0,6	No	-	No	No	-	-
1591303	J-Y(ST)Y...LG 4x2x0,6	No	-	No	No	-	-
1591305	J-Y(ST)Y...LG 6x2x0,6	No	-	No	No	-	-
1591307	J-Y(ST)Y...LG 10X2X0,6	No	-	No	No	-	-
16000003	NYM-J 3G1,5	No	-	No	No	-	-
16000023	NYM-J 5G1,5	No	-	No	No	-	-
16000063	NYM-J 5G2,5	No	-	No	No	-	-
16000213	NYM-J 3G2,5	No	-	No	No	-	-
1600103	H07RN-F 3G1,5	No	-	No	No	-	-
16001043	H07RN-F 5G1,5	No	-	No	No	-	-
1600118	H07RN-F 3G2,5	No	-	No	No	-	-
16001293	H07RN-F 5G2,5	No	-	No	No	-	-
16001303	H07RN-F 5G4	No	-	No	No	-	-
1600187	H07RN-F 2X2,5	No	-	No	No	-	-
1600200	H05RR-F 3G1,5	No	-	No	No	-	-
16002023	H05RR-F 5G1,5	No	-	No	No	-	-
1600207	H05RR-F 3G0,75	No	-	No	No	-	-

U.I. Lapp GmbH - REACH / RoHS Substance Information



Date: 02.04.2025

Article Information		REACH - SVHC (June 27th 2024)		RoHS (2011/65/EU - (EU) 2015/863)			
Material part number	Designation	Contains the product a SVHC above 0,1 %?	Name of SVHC	RoHS restricted substances contained exceeding limit values?	Exemption used?	Number of exemption	Description
1600209	H05RR-F 3G2,5	No	-	No	No	-	-
16002133	H05RR-F 5G2,5	No	-	No	No	-	-
1600302	NSGAFÖU 1,8/3kV 1x4	No	-	No	No	-	-
1600304	NSGAFÖU 1,8/3kV 1x10	No	-	No	No	-	-
1601126	H05VV-F 5G2,5 WH	No	-	No	No	-	-
1601204	H03VV-F 3G0,75 BK	No	-	No	No	-	-
1601211	H03VV-F 4G0,75 BK	No	-	No	No	-	-
1708002	(J)-Y(ST)Y...LG 2X2X0,8 BMK	No	-	No	No	-	-
2170000	Coaxial - RG 58 C/U	No	-	No	No	-	-
2170001	Coaxial - RG-174 A/U	No	-	No	No	-	-
2170012	Coaxial - RG-59 B/U	No	-	No	No	-	-
2170126	UNITRONIC LAN 200 F/UTP Cat. 5e	No	-	No	No	-	-
2170138	UNITRONIC LAN 200 SF/UTP Cat.5e LSZH	No	-	No	No	-	-
2170172	UNITRONIC LAN 200 F/UTP Cat.5eLSZH FLEX	No	-	No	No	-	-
2170195	UNITRONIC LAN 500 U/FTP Cat.6A LSZH	No	-	No	No	-	-
2170196	UNITRONIC LAN 500 F/FTP Cat.6A LSZH	No	-	No	No	-	-
2170240	UNITRONIC BUS EIB 2X2X0,8	No	-	No	No	-	-
2170614	UNI LAN1000 S/FTP Cat.7LSZH 4x2xAWG23/1	No	-	No	No	-	-
2210700	H01N2-D 1X16	No	-	No	No	-	-
28000001	HITRONIC POF SIMPLEX PE	No	-	No	No	-	-
3028243	H05VV-F 5G2,5 BK	No	-	No	No	-	-
3034033	LAPP KABEL KOAXIAL 75 Ohm VIDEO GN	No	-	No	No	-	-
38007255	H07V-U 1X1,5 BK	No	-	No	No	-	-
38007259	H07V-U 1X1,5 BU	No	-	No	No	-	-
4520001	H07V-K 1X1,5 GNYE	No	-	No	No	-	-
4520006	H07V-K 1X16 GNYE	No	-	No	No	-	-
4520011	H07V-K 1X1,5 BK	No	-	No	No	-	-
4520021	H07V-K 1X1,5 BU	No	-	No	No	-	-
4520041	H07V-K 1X1,5 RD	No	-	No	No	-	-
4560023	LiFY 1X1 BK	No	-	No	No	-	-
4560023S	LiFY 1X1 BK	No	-	No	No	-	-
4560024	LiFY 1X1 BU	No	-	No	No	-	-
4560024S	LiFY 1X1 BU	No	-	No	No	-	-
4560026	LiFY 1X1 RD	No	-	No	No	-	-
49900001	SiL-(N)2GFAZ 2X0.5 (TINNED) 300V BK	No	-	No	No	-	-
49900002	SiL-(N)2GFAZ 2X0.75 (TINNED) 300V BK	No	-	No	No	-	-
49900007	MICROPHONE 2X0,14 BARE/PVC/C/PVC BK	No	-	No	No	-	-
49900008	MICROPHONE 3X0,08 BARE/PVC/C/PVC BK	No	-	No	No	-	-
49900009	MICROPHONE 4X0,14 BARE/PVC/C/PVC BK	No	-	No	No	-	-
49900013	TELEPHONE FLAT PP/PVC 6xAWG28/7 BK	No	-	No	No	-	-
49900019	LAN CAT.5E 100MHZ F/UTP LSZH 4X2XAWG26/7	No	-	No	No	-	-
49900022	LAN CAT.6 350MHZ SF/UTP LSZH 4X2XAWG23/1	No	-	No	No	-	-
49900045	FLACHBAND 300V 8X(7X0.203) GRID 2.5 mm	No	-	No	No	-	-
49900046	FLACHBAND 300V 20X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-
49900049	FLACHBAND 300V 26X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-
49900051	FLACHBAND 300V 40X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-
49900054	FLACHBAND 300V 10X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-
49900055	FLACHBAND 300V 14X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-

U.I. Lapp GmbH - REACH / RoHS Substance Information



Date: 02.04.2025

Article Information		REACH - SVHC (June 27th 2024)		RoHS (2011/65/EU - (EU) 2015/863)			
Material part number	Designation	Contains the product a SVHC above 0,1 %?	Name of SVHC	RoHS restricted substances contained exceeding limit values?	Exemption used?	Number of exemption	Description
49900056	FLACHBAND 300V 16X(7X0.127) GRID 1.27 mm	No	-	No	No	-	-
49900057	SPEAKER FLATTWIN 2X2,5 slvrdfine PVC TR	No	-	No	No	-	-
49900058	SPEAKER FLATTWIN 2X4 slvrdfine PVC TR	No	-	No	No	-	-
49900063	H03VV-F 2X0,75 BK	No	-	No	No	-	-
49900065	H03VV-F 2X0,75 WH	No	-	No	No	-	-
49900068	H03VV-F 3G0,75 WH	No	-	No	No	-	-
49900069	H03VV-F 4G0,75 WH	No	-	No	No	-	-
49900071	H05RNH2-F 2X1,5 GN	No	-	No	No	-	-
49900075	H05VV-F 3G1 BK	No	-	No	No	-	-
49900076	H05VV-F 3G1 WH	No	-	No	No	-	-
49900077	H05VV-F 3G1,5 BK	No	-	No	No	-	-
49900078	H05VV-F 3G1,5 WH	No	-	No	No	-	-
49900080	H05VV-F 5G1,5 WH	No	-	No	No	-	-
49900081	H05VVH2-F 2X0,75 BK	No	-	No	No	-	-
49900082	H05VVH2-F 2X0,75 WH	No	-	No	No	-	-
49900133	LIFY 1X0,25 BK	No	-	No	No	-	-
49900135	LIFY 1X0,25 GN	No	-	No	No	-	-
49900136	LIFY 1X0,25 RD	No	-	No	No	-	-
49900144	LIFY 1X1 GN	No	-	No	No	-	-
49900149	LIFY 1X2,5 BK	No	-	No	No	-	-
49900151	LIFY 1X2,5 RD	No	-	No	No	-	-
49900152	LIFY 1X2,5 YE	No	-	No	No	-	-
49900153	MICROPHONE 2X0,5 TND/PVC/TNDC/PVC BK	No	-	No	No	-	-
49900154	MICROPHONE 4X0,5 TND/PVC/TNDC/PVC BK	No	-	No	No	-	-
49900173	LiY-Z 2X1 RD+RDBK	No	-	No	No	-	-
49900177	LiY-Z 2X4 GY	No	-	No	No	-	-
49900179	LiY-Z 2X2,5 BK	No	-	No	No	-	-
49900180	LiY-Z 2X2,5 BN	No	-	No	No	-	-
49900182	LiY-Z 2X2,5 WH	No	-	No	No	-	-
49900183	LiY-Z 2X1,5 BK	No	-	No	No	-	-
49900185	LiY-Z 2X1,5 WH	No	-	No	No	-	-
49900187	NYIF-J 3G1,5	No	-	No	No	-	-
49900197	UNITRONIC SPEAKER LIYY BK 2x2,5 (BK+YE)	No	-	No	No	-	-
49900200	MICROPHONE 7X0,5 TND/PVC/TNDC/PVC BK	No	-	No	No	-	-
49900202	MICROPHONE 5X0,14 BARE/PVC/C/PVC BK	No	-	No	No	-	-
49900203	TELEPHONE FLAT PP/PVC 4xAWG28/7 BK	No	-	No	No	-	-
49900206	PVCSHTH ALERT 150V4X0,14 18X0.1ALLWH	No	-	No	No	-	-
49900208	MICROPHONE 2X0,75 TND/PVC/TNDC/PVC BK	No	-	No	No	-	-
49900211	LIFY 48 VAC 1X4 TIN-COATED TRANSPARENT	No	-	No	No	-	-
49900214	LIFY 48 VAC 1X6 TIN-COATED TRANSPARENT	No	-	No	No	-	-
49900215	MICROPHONE 1X0,14 BARE/PVC/C/PVC BK	No	-	No	No	-	-
49900216	NV-24V Si/PVC 2X1,5 (RD+BU) 105°C BK	No	-	No	No	-	-
49900217	NV-24V Si/PVC 2X2,5 (RD+BU) 105°C BK	No	-	No	No	-	-
49900218	NV-24V Si/PVC 2X4 (RD+BU) 105°C BK	No	-	No	No	-	-
49900219	SIL-SIFF 1X1 (0,05MM TINNED) OD2,5MM BK	No	-	No	No	-	-
49900222	SIL-SIFF 1X1 (0,05MM TINNED) OD2,5MM RD	No	-	No	No	-	-
49900224	SIL-SIFF 1X0,25 (0,05mm TINNED) BK	No	-	No	No	-	-
49900230	JALOUSIE C. TPE/PUR 300/500V 4X0,75 WH	No	-	No	No	-	-

U.I. Lapp GmbH - REACH / RoHS Substance Information



Date: 02.04.2025

Article Information		REACH - SVHC (June 27th 2024)		RoHS (2011/65/EU - (EU) 2015/863)			
Material part number	Designation	Contains the product a SVHC above 0,1 %?	Name of SVHC	RoHS restricted substances contained exceeding limit values?	Exemption used?	Number of exemption	Description
49900231	Instrumentenkabel 1x0,22 TPE	No	-	No	No	-	-
49900237	LiY-Z 2X0,14 RD+RDBK	No	-	No	No	-	-
49900245	BELL WIRE 2X0,8 TND/PVC WH/BN	No	-	No	No	-	-
49900248	LiY-Z 2X2,5 RD+RDBK	No	-	No	No	-	-
49900249	LiY-Z 2X0,5 BK	No	-	No	No	-	-
49900250	LiY-Z 2X0,5 WH	No	-	No	No	-	-
49900255	LiY-Z 2X0,38 RD+RDBK	No	-	No	No	-	-
49900257	LiY-Z 2X0,75 BK	No	-	No	No	-	-
49900258	LiY-Z 2X0,75 BN	No	-	No	No	-	-
49900259	LiY-Z 2X0,75 WH	No	-	No	No	-	-
49900264	WH-SHTH PVC YRBELLWIRECABLE 4x0.8mmBARE	No	-	No	No	-	-
49900272	(L)iyv 80°C 1X0,08 TIN-COATED ROHS BK	No	-	No	No	-	-
49900276	BELL WIRE 1X0,8 TND/PVC WH	No	-	No	No	-	-
49900281	TELEPHONE LiYY 8x0,14 BK	No	-	No	No	-	-
49900284	TELEPHONE LiYY 4x0,14 GY	No	-	No	No	-	-
61831047	Kabelbinder Basic Tie 290x3.5 BK	No	-	No	No	-	-
7027055	ÖLFLEX TRUCK 170 TWIN 2x6/TÜ.EGG.091-04	No	-	No	No	-	-
7027067	ÖLFLEX TRUCK 170 FLRY 7x1,5	No	-	No	No	-	-