

# CONNECT

#### P | Cabling

We realize ideas

#### **Data sheet**

Page 1/7


#### Patch cord 6kV Flex500 Outdoor 5.0 m black

P/N 13084F5000-E EAN 4251394639918


> 2023/05/16 Version: G

#### Illustrations





Dimensional drawing



See enlarged drawings at the end of document

#### **Product specification**

- · RJ45 patch cord for industrial and outdoor applications
- shielded Cat.5e, Class E<sub>A</sub> RJ45 patch cord
- compliance with class EA Channel-Link acc. to ISO/IEC 11801-1, DIN EN 50173-1
- · tested: Channel-Link up to 500 MHz
- suitable 10 GBit/s Ethernet (IEEE 802.3an) up to 40 m
- · especially suitable for unshielded and shielded Class EA systems
- · robust and abrasion-resistant cable for industrial applications, such as machine and plant construction. Also suitable for outdoor installation
- meeting the VDE-AR-N 4100:2019-04 (6KV impulse voltage test according to DIN EN 60664-1) for installation in metering position and electrical distribution panels
- cable type: S/UTP 4x2xAWG24/7
- cable sheath: LSHF (FRNC) PUR, black
- the cable is designed for repeated moving application (drag chain). Tested with a bending radius of 100mm and an acceleration of 4m/s², 3 million cycles at room temperature were achieved.
- two shielded RJ45 connectors; 1:1 assignment
- UV and oil-resistant
- Remote Powering (PoE, PoE plus and UPoE)
- suitable for IoT, M2M IoT, HDBaseT, industry 4.0, multimedia, wideband video
- · molded snagless anti-bend sleeve
- considerably longer durability than standard patch cords
- · very short cable boot







We realize ideas

Data sheet
Patch cord 6kV Flex500 Outdoor 5.0 m black

Page 2/7

P/N 13084F5000-E EAN 4251394639918

> 2023/05/16 Version: G

		Version: G
Technical Data		
General Data		
Fields of application	Industrial Ethernet harsh environment Distributed building services Automated Infrastructure Management (AIM) Tertiary	
Mechanical measurement according to MICE	M1	
Ingress measurement according to MICE	I1	
Climatic measurement according to MICE	C1	
Electromagnetic measurement according to MICE	E2	
Design	patch cord	
Shielding	shielded	
Transmission technology	Copper	
Cable Type	S/UTP	
Number of twisting elements	4	
Twisting element	Pair	
Wiring	1 - 1	
Color	black	
Dimensions		
Dimension - Interface 1 (L x W x H)	27.4 mm x 13.71 mm x 15.5 mm	
Dimension - Interface 1 (L x W x H)	1.079 in. x 0.54 in. x 0.61 in.	
Dimension - Interface 2 (L x W x H)	27.4 mm x 13.71 mm x 15.5 mm	
Dimension - Interface 2 (L x W x H)	1.079 in. x 0.54 in. x 0.61 in.	
Cable length (m)	5 m	
Cable length (ft)	16.4 ft	
Weight	71.8 kg/km	
Marking option	by cable boot	
Transmission characteristics		
Category (ISO)	5	
Class (ISO/IEC)	E <sub>A</sub>	
Category (TIA)	5e	
Remote Powering	yes	
PoE	IEEE 802.3af	
D.E. I.	IEEE 000 0 4	

IEEE 802.3at



PoE plus





We realize ideas

Data sheet
Patch cord 6kV Flex500 Outdoor 5.0 m black

**Page 3/7** 

P/N 13084F5000-E EAN 4251394639918

> 2023/05/16 Version: G

Version:
yes
yes
IEEE 802.3u
IEEE 802.3ab
IEEE 802.3an
RJ45 plug
RJ45 plug
1
1
1
1
8P/8C
8P/8C
AWG 24/7
0.227 mm² - 0.227 mm²

Electrical characteristics	
Current carrying capacity	max. 1 A
Rated voltage	max. 60 V DC

0.61 mm - 0.61 mm

0.024 in. - 0.024 in.

0.96 mm - 0.96 mm

0.038 in. - 0.038 in.

8 mm - 8 mm 33.9 kg/km





Conductor diameter, stranded wire (bare copper)

Conductor diameter, stranded wire (bare copper)

Core diameter (conductor with insulation)

Core diameter (conductor with insulation)

Cable sheath diameter (min. - max.)

Core diameter (min. - max.)

Cable sheath diameter

Copper index



We realize ideas

## Data sheet Patch cord 6kV Flex500 Outdoor 5.0 m black

Page 4/7

P/N 13084F5000-E EAN 4251394639918

> 2023/05/16 Version: G

	version: e
Technical Data	
Electrical characteristics	
Rated test voltage	
Rated test voltage core / cable jacket acc. to DIN EN 60664-1	6000 V
Rated test voltage shield / cable jacket acc. to DIN EN 60664-1	6000 V
Rated test voltage core / shield	1500 V
Rated test voltage core / core	800 V
Contact resistance	max. 20 mOhm
Through resistance	max. 200 mOhm
Insulation resistance	min. 1000 MOhm
Resistance unbalance	max. 2 %
Capacitance at 800 Hz	Nom. 45 nF/km
Capacitance unbalance pair to ground	max. 1200 pF/km
Nominal velocity of propagation	ca. 65 %
Delay skew	max. 45 ns/100 m
Dielectric strength conductor-conductor (primarily)	max. 500 V DC
Dielectric strength conductor-conductor (primarily)	max. 500 V AC
Dielectric strength conductor-conductor (secondary)	max. 500 V DC
Dielectric strength conductor-conductor, peak value (secondary)	max. 500 V AC
Mechanical data	
Tensile force	100 N
Position/mounting of latch standard installation position	top
Bending radius without load	max. 60 mm
Bending radius with load	max. 80 mm
Number of alternating bending cycles (mechanical resistance) at:	max. 8500
Alternating bending radius	100 mm
acceleration	4 m/s²





We realize ideas

Data sheet
Patch cord 6kV Flex500 Outdoor 5.0 m black

Page 5/7

P/N 13084F5000-E EAN 4251394639918

> 2023/05/16 Version: G

Materials and material properties		
Material - Conductor	Cu (copper)	
Material - Conductor Insulation	Polyethylene	
Material - Cable jacket	PUR	
Material - Inner cable jacket	HFFR	
Material - Plug housing interface 1	PC (polycarbonate)	
Material - Plug housing interface 2	PC (polycarbonate)	
Material - Contact interface 1	CuSn (tin bronze)	
Material - Contact interface 2	CuSn (tin bronze)	
Material - Contact finish interface 1	Au (gold)	
Material - Contact finish interface 2	Au (gold)	
Material - Contact carriers interface 1	Plastics	
Material - Contact carriers interface 2	Plastics	
Material - Shield interface 1	CuSn (tin bronze)	
Material - Shield interface 2	CuSn (tin bronze)	
Material - Shield finish interface 1	Sn (tin)	
Material - Shield finish interface 2	Sn (tin)	
Material - Main shield	Cu (copper) braid	
Flame retardancy	yes	
Halogen free	yes	
Oil resistance	yes	
UV-resistance	yes	
drag chain suitable	yes	

Environmental conditions		
Temperature (min max.)		
Temperature - Storage °C	-40 °C - 70 °C	
Temperature - Storage °F	-40 °F - 158 °F	
Temperature - Operating °C	0 °C - 50 °C	
Temperature - Operating °F	32 °F - 122 °F	
Temperature - Installation °C	0 °C - 50 °C	
Temperature - Installation °F	32 °F - 122 °F	







We realize ideas

Data sheet
Patch cord 6kV Flex500 Outdoor 5.0 m black

Page 6/7

P/N 13084F5000-E EAN 4251394639918

> 2023/05/16 Version: G

Technical Data	
Standards/Regulations	
Generic cabling systems	
General requirements	ISO/IEC 11801-1   DIN EN 50173-1 ANSI/TIA-568.2-D
Test for vertical flame propagation for a single insulated wire or cable	IEC 60332-1
Measurement of smoke density of cables burning	IEC 61034
Determination of acidity (by measuring the pH value) and conductivity	IEC 60754-2
Specification for the testing of balanced and coaxial inform	ation technology cabling
Cords as specified in ISO/IEC 11801 and related standards	IEC 61935-2
Classifications	
ETIM 7.0	EC001262
ETIM 8.0	EC001262
ETIM 9.0	EC001262







We realize ideas

Data sheet
Patch cord 6kV Flex500 Outdoor 5.0 m black

Page 7/7

P/N 13084F5000-E

EAN 4251394639918 2023/05/16

Version: G

#### Illustrations

