

tesa - RDS

Regulatory Data Sheet

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing tesa products is allowed provided that: the information is copied in full with no changes

tesa® 4008, 4011, 4012, 4089, 4156, 4172, 4185, 4280, 4282, 4344, 4364, 4368, 4368PV1, 4373, 4380, 4386, 4388, 4411PV0, 4428, 4440, 4559, 4590, 4591, 4600PV0, 4613, 4662, 4663PV1, 4665, 4668, 4688, 4840, 4843, 4844, 4848, 4940, 4943PV4, 4985PV9, 5056, 5391, 5395, 5412, 5418, 5428, 5430, 5432, 5433, 5454, 5503, 5559, 6024, 6074, 6076, 6300, 6400, 6813, 6875, 7042, 7055, 7255PV42T, 7272PV44G, 7273PV44G, 7274PV44G, 45063, 45065, 50378, 50565PV1, 50575PV0, 50577, 50600, 51407PV1, 51408PV0, 52064, 52110, 52210, 52215, 53123, 53128, 53315, 53317, 53319, 53393, 53398, 53799PV2, 53903, 53947, 53948, 53949, 53959, 53988PV0, 55157, 55193, 55228, 55239, 55297, 55298, 55387, 55388, 55396, 55419, 55446, 55587, 55604, 55701, 55703, 55706, 56064, 56190PV22, 56192PV22, 56193PV2, 56201PV22, 56205PV22, 56223, 56244PV2, 56244PV22, 56349, 56359, 56496, 56578, 56587, 56588, 56622, 56623, 56865, 56866, 56250, 56251, 56270, 56271, 57443, 57447, 57653, 57689, 57890, 57898, 57910, 57981, 57982, 57983, 57984, 58263, 58326, 58327, 58328, 58395, 58398, 58370, 58451PV0, 58452PV0, 58522PV1, 58523PV1, 58610, 58611, 58612, 58613, 59100, 59405, 59810, 59840, 59841, 59880, 59881, 60020, 60021, 60022, 60040, 60042, 60077, 60100, 60101, 60150, 60151, 60152, 60153, 60160, 60161, 60162, 60166, 60272, 60362, 60632PV0, 60650, 60651, 60652, 60670, 60672, 60703, 60760, 60943, 60950, 60951, 60973, 60975, 60977, 60996, 61127, 61128, 61131, 62455, 62600, 63632, 63652PV0, 64006, 64264, 66001, 66891, 67001, 68144, 68616PV43, 68618, 69802, 77108PV28, 77112PV28, 88641, 88642, 88643PV43, 88644, 88665, 88708, 88710, 88712, 88720

tesa® Stick: 57024, 57026, 57030, 57047, 57048, 57076, 57084, 57087, 57088, 57272, 58559, 58561

We declare that a.m. articles, to the best of its knowledge, do not contain chemicals in concentrations about the legal limits, specified in the regulations mentioned below. Further we declare that a.m. products, to the best of its knowledge, do comply to the regulations mentioned below.

Regulations

EU REACH (Regulation 1907/2006/EU)

The a.m. articles, including any article that the products are composed of, does not contain at today's level of awareness any of the substances published in the candidate list (SVHC) by the European Chemical Agency (ECHA) in a concentration of more than 0,1 mass percentage.

<https://echa.europa.eu/web/guest/candidate-list-table>

The a.m. articles are not subject of the restrictions of annex XVII. This statement covers

the status at that time of writing this letter.

<https://echa.europa.eu/de/substances-restricted-under-reach>

Publication of Annex XIV on the web site of European Chemicals Agency (ECHA):

<https://echa.europa.eu/de/authorisation-list>

WEEE directive (2012/19/EU), RoHS directive 2011/65/EC incl. RoHS directive III 2015/863/EC

The a.m. articles, including any article that the products are composed of, do not exceed the maximum concentration values at today's level of awareness of the following substances:

- Lead (Pb) 0,1 %
- Mercury (Hg) 0,1 %
- Cadmium (Cd) 0,01 %
- Hexavalent chromium (Cr6+) 0,1 %
- Polybrominated biphenyls (PBB) 0,1 %
- Polybrominated diphenyl ether (PBDE) 0,1 %
- Bis(2-ethylhexyl) phthalate (DEHP) 0,1 %
- Butyl benzyl phthalate (BBP) 0,1 %
- Dibutyl phthalate (DBP) 0,1 %
- Diisobutyl phthalate (DIBP) 0,1 %

POPs (Persistent Organic Pollutants) Regulation 2019/1021/EC

The a.m. articles, including any article that the products are composed of, do not contain at today's level of awareness Persistent Organic Pollutants.

Substances that deplete the Ozone Layer: Regulation 1005/2009/EC

The a.m. articles, including any article that the products are composed of, do not contain Substances that deplete the Ozone Layer acc. 1005/2009/EC.

European packaging and packaging waste Regulation 94/62/EC incl. 2018/852/EC

The a.m. articles are compliant with 94/62/EC incl. 2018/852/EC and do not contain substances restricted per regulation.

TSCA Section 6

The a.m. articles do not contain:

- Phenol, isopropylated phosphate (3:1) (PIP (3:1), CAS 68937-41-7)
- Hexachlorobutadiene HCBd, CAS 87-68-3
- Decabromodiphenyl Ether decaBDE, CAS 1163-19-5
- Pentachlorothiophenol PCTP, CAS 133-49-3
- 2,4,6-Tri-tert-butylphenol 2,4,6-TTBP, CAS 732-26-3

This document is electronically generated and valid without signature.

Disclaimers:

The information provided in this document are provided according best knowledge and may be based partly on information provided by suppliers of tesa SE or its affiliates. For completeness, reliability and strictness of the information, tesa SE cannot guarantee.



Enlargements of regulations after the date of issuance of this document are not part of this document.

tesa SE recommends the user determine whether the product is fit for the users' specific purpose and is suitable for the users' method of application.

tesa SE and its affiliates are not liable for any consequential, incidental or special damages or loss of profit incurred by customers.