

Intel Core i5 i5-14500 - 2.6 GHz - 14 Kerne - 20 Threads

24 MB Cache-Speicher - FCLGA1700 Socket - Box

Gruppe	Prozessoren
Hersteller	Intel
Hersteller Art. Nr.	BX8071514500
EAN/UPC	5032037279178



Beschreibung

Intel Core i5 i5-14500 - 2.6 GHz - 14 Kerne - 20 Threads - 24 MB Cache-Speicher - FCLGA1700 Socket - Box

Hauptmerkmale

Produktbeschreibung	Intel Core i5 i5-14500 / 2.6 GHz Prozessor - Box
Produkttyp	Prozessor
Prozessortyp	Intel Core i5 i5-14500 (14th Gen)
Anz. der Kerne	14 Kerne / 20 Threads
Cache-Speicher	24 MB
Integrierte Grafik	Intel UHD Graphics 770
Geeignete Sockel	FCLGA1700 Socket
Prozessoranz.	1
Taktfrequenz	2.6 GHz (P-Kern) / 1.9 GHz (E-Kern)
Max. Turbo-Taktfrequenz	5 GHz (P-Kern) / 3.7 GHz (E-Kern)
Herstellungsprozess	10 nm
Funktionen	Enhanced SpeedStep technology, Hyper-Threading-Technologie, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Intel Trusted Execution Technology, Streaming-SIMD-Erweiterungen 4.1, Streaming-SIMD-Erweiterungen 4.2, Intel Turbo Boost Technology 2.0, Intel AES New Instructions (AES-NI), Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Secure Key, Intel Advanced Vector Extensions 2 (AVX2.0), Intel Turbo Boost Max Technology 3.0, Intel Speed Shift Technology, Mode-based Execute Control (MBE), Intel Volume Management Device (VMD), Intel Boot Guard, Intel Smart Sound Technology, Intel Wake on Voice, Intel Adaptix Technology, Intel Control-Flow Enforcement Technology, Intel Gaussian and Neural Accelerator 3.0, Intel Thread Director, MIPI SoundWire 1.2, Intel Stable IT Platform Program (SIPP), Intel Standard Manageability (ISM), Intel Virtualization Technology with Redirect Protection (VT-rp), Direct Media Interface (DMI), Multi-Format Codec Engines

Technische Daten © 1WorldSync. Technische Änderungen und Irrtümer vorbehalten.