PH METER

ISO-9001, CE, IEC1010



FEATURES

- * High quality & general purpose pH measurement.
- * Easy operation, compact size.
- * Water resistance on the front panel.
- * All function keys are used the rubber button.
- * Large LCD display.
- * 0 to 14 pH x 0.01 pH
- * High input impedance.
- * Not necessary to adjust the pH range Temperature Compensation



PH METER

FEATU	RES
* High quality & general purpose pH measurement.	* Water resistance on the front panel.
* Easy operation, compact size.	* All function keys are used the rubber button.

OFNIEDAL DECODIDELONO					
GENERAL DESCRIPTIONS					
Display	LCD, 21.5 mm (0.7") digit height.				
Measurement	0 to 14 pH x 0.01 pH				
Resolution					
Accuracy	± 0.07 pH (pH5 to pH 9) ± 0.1 pH (pH 4 to pH 10)				
Accuracy	± 0.2 pH (pH 1 to pH 3.9, pH 10.1 to pH 13)				
	* Main instrument only.				
Input Impedance	10 ohms.				
PH range Temp.	No adjust.				
Compensation	No adjust.				
Dala Hold	To feeze the measured pH value on the display.				
Sampling Time	Approx. 0.4 second.				
Operating Temp.	0 to 50 °C (32 to 122°F)				
Operating	Less than 80% RH.				
Humidity					
Calibration Knob	External PH 4 (slope adj.) & PH 7 (Cal. adj.).				
Power Supply	006P DC 9V battery.				
Power	Approx. 2.0 mA.				
Consumption					
Dimension	205 x 68 x 30 mm (8.1 x 2.7 x 1.2 inch).				
Weight	220 g/0.48 LB.				
pH electrode	Any connector pH Electrode with BNC connector.				
(Optional)					
Standard	Instruction Manual1 PC.				
Accessories					
Optional	pH electrode.				
Accessories	pH 4.0 buffer solution, pH 7.0 buffer solution.				

APPLICATIONS					
* AQUARIUMS	* PAPER INDUSTRY	* FOOD PROCESSING	* SCHOOLS & COLLEGES		
* BEVERAGE	* PLATING INDUSTRY	* PHOTOGRAPHY	* SWIMMING POOLS		
* FISH HATCHERIES	* QUALITY CONTROL	* LABORATORY	* WATER CONDITIONING		

OPTIONAL ACCESSORIES				
pH ELECTRODE	General purpose pH electrode with BNC conector.			
PE-03	Range: 1 to 13 pH (typical 0 to 14 pH).			
	Expoxy body, Body size: 12 mm dia. x 160 mm.			
	Cable length: 1 meter.			
pH ELECTRODE	General purpose & high quality pH electrode with BNC conector.			
PE-11	Range: 1 to 13 pH (typical 0 to 14 pH).			
	Expoxy body, Body size: 9.5 mm dia. x 120 mm.			
	Cable length: 2 meter.			
pH ELECTRODE	Professional, laboratory &			
PE-01	field usage. 9.5 mm dia. x 130 mm.			
	Epoxy body, 0 - 14 pH.			
	Cable length: 1 meter.			
SPEAR TIP	The "Spear Tip pH electrode " is perfect for those pH			
PH ELECTRODE	measurements in applications where sample piercing is required.			
Model: PE-04HD	Meat, sausage and cheese are ideal applications. The electrode			
	features a very durable glass measuring spear packaged in a			
	rugged virtually unbreakable epoxy body.			
	Measuring range: 0 to 14 pH.			
	Size 12 mm dia. x 150 m.			
BUFFER SOLUTION	PH 7.00 standard buffer solution.			
PH-07				
BUFFER SOLUTION	PH 4.00 standard buffer solution.			
PH-04				
Carrying case	Hard carrying case, CA-06			

^{*} Appearance and specifications listed in this brochure are subject to change without notice.