



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

SLC-100

SOUND LEVEL CALIBRATOR

Nº 10 12 91

CE

VERSION 12/21

This sound level calibrator is suitable for adjusting and testing the accuracy of sound level measurement devices. The calibrator generates a defined sound signal with a switchable sound level of 94 dB or 114 dB. Microphones with a diameter of 12.7 mm (0.5 inches) can be inserted in the calibration chamber. The accuracy of the device complies with the Directive IEC 60942-2003 Class 2.

HIGHLIGHTS

Switchable sound level //

Sealed calibration chamber //

Corresponds to IEC 60942 class 2 //



GENERAL SPECIFICATIONS

FOR MICROPHONES WITH A Ø OF: 12.7 mm (1/2") **OUTPUT FREQUENCY:** 1 kHz \pm 4 %, sine **OUTPUT LEVEL:** 94 dB or 114 dB **VOLTAGE SUPPLY:** 9 V block alkaline battery **WEIGHT:** 278 g **DIMENSIONS (W x H x D):** 50 x 120 x 42 mm

TECHNICAL DATA

Power consumption:	approx. 4 mA
Reference Conditions	
- Temperature:	23 °C
- Relative air humidity:	65 %
- Atmospheric pressure:	1013 hPa
Temperature coefficient:	\pm 0.02 dB/°C
Accuracy output level:	\pm 0.5 dB (at 94 dB) / \pm 1.0 dB (at 114 dB) under reference conditions
Battery life:	approx. 40 hrs (alkaline battery)
Operating temperature:	0 °C to +50 °C
Storage conditions:	-20 °C to +60 °C, < 80 % relative humidity

PACKAGE CONTENT

Sound level calibrator // 9 V battery // Case // Operating instructions

This data sheet is published by Voltcraft®, Lindenweg 15, D-92242 Hirschau / Germany, Phone +49 180 586 582 7. The data sheet reflects the current technical specifications at time of print. We reserve the right to change the technical or physical specifications.