

FLUX REAR

Mid Tower Case

FLOW LUXURY


FLUX Platform, abbreviation of Flow Luxury, features ultra case structure design for excellent airflow and 5 fans included, delivering enhanced GPU cooling performance.

FLUX Platform Patent Number: 11259440

FLUX AIRFLOW

Multi-directional vent design, featuring extensive air intakes at the bottom, power supply chamber and lower sides, along with top vents and large-area mesh at the front, creating a dedicated Antec Flux airflow channel.

MULTI-DIRECTIONAL VENT DESIGN



PRE-INSTALLED 5 X HIGH-PERFORMANCE PWM FANS



FLUX VERTICAL COOLING

Designed with a front-mounted PSU chamber, this layout opens up space for improved airflow at the bottom of the case, enhancing heat dissipation around the graphics card.

FLUX HORIZONTAL COOLING

Air intake via the front mesh provides a smooth venting channel throughout the case.

OPTIMIZED CHASSIS DESIGN

The recessed front design enhances airflow while minimizing noise for better thermal and acoustic performance.

SUPPORTS 360MM WATER COOLING AT THE TOP

- Supports 140mm rear fan installation with radiator thickness ≤ 65mm.
- Supports 120mm rear fan installation with radiator thickness between 55-70mm.



BOTTOM AIR INTAKE OPTIMIZATION

The front-mounted PSU chamber preserves an open, spacious airflow path at the bottom that is free of hard drives, enabling efficient, direct cooling of the GPU through reverse fans.



PREMIUM WOOD

The front panel is crafted with a combination of metal mesh and premium wood to create a high-quality texture.



BUILT-IN GPU BRACKET


Includes a support bracket compatible with high-performance graphics cards.

SUPPORT BACK-CONNECT MOTHERBOARDS

Plug in cables from behind to give front a cleaner look and a smoother airflow channel.



TOOL-FREE PANEL DESIGN



FRONT-MOUNTED PSU CHAMBER & 13A EXTENSION CABLE

The front-mounted PSU chamber improves airflow by freeing up internal space, while the included 13A extension cable ensures stable power delivery for high-wattage PSUs.

POWER EXTENSION CABLE SETUP




CABLE MANAGEMENT

Equipped with grommets and Velcro straps for easy, secure cable management, enhancing airflow and creating a cleaner look.



I/O PANEL

Dust plugs included.



EXTENSIVE INTERIOR

• Motherboard support	ATX, Micro-ATX, ITX	• Power Supply max length (Without cable) 170mm	• 3.5"	1
• CPU cooler max height	≤ 180 mm	• 2.5"	2	
• GPU max length	≤ 400 mm			



SPECIFICATION

Main Spec Motherboard Support: ATX, Micro-ATX, ITX Form Factor: Mid Tower Case Material: Steel + Plastic + Wood Side Window Material: 4mm Tempered Glass I/O Ports: Power, LED Control Button, USB 3.0 x 2, Type-C 3.2 Gen 2 (10Gbps) x 1, Headphone/Mic Combo Jack Case Dimensions (DxWxH): 460 x 240 x 460 mm Box Dimensions (DxWxH): 510 x 314 x 530mm Compatibility & Clearances CPU Cooler Max Height: ≤ 180mm GPU Max Length: ≤ 400mm Power Supply Max Length: (Without cable) 170mm Fan Support Front: 2 x 140mm Top: 3 x 120mm / 2 x 140mm Power Supply Shroud: 2 x 120mm Rear: 1 x 120mm / 1 x 140mm Included Fan(s): 2 x 140mm ARGB PWM fans at the front + 2 x 120mm PWM reverse fans on the PSU shroud + 1 x 140mm ARGB PWM fan at the rear	Radiator Support Top: Up to 360mm Rear: Up to 120mm Expansion Slots Standard: 7 Drive Bays 3.5": 1 2.5": 2 General Dust Filter: Bottom Net Weight: 8.18 kg Gross Weight: 9.72 kg Warranty: 2 years UPC#: 6-761345-10241-4
---	--