

Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

ACRYLIC PAINT
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Paints

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe BV
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
Extremely flammable aerosol.
Pressurised container: May burst if heated.

Classification is based on test data.



Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)
Creationdate : 03.12.20 Version : 1.0
Replaces:

Health: Eye irritation, category 2
 Causes serious eye irritation.
 Specific target organ toxicity - single exposure, category 3
 May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Not classified

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
 acetone; propan-2-one; propanone
 n-butyl acetate

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
 H229 : Pressurised container: May burst if heated.
 H319 : Causes serious eye irritation.
 H336 : May cause drowsiness or dizziness.

Precautionary statement(s): P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 : Do not spray on an open flame or other ignition source.
 P251 : Do not pierce or burn, even after use.
 P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether	01-	115-	204-	25-	Flam. Gas 1. Press. Gas	H220.H280	A



Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

	2119472128-37	10-6	065-8	50			
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	10-25	Flam. Liq. 3, STOT SE 3	H226,H336	
ethyl acetate	01-2119475103-46	141-78-6	205-500-4	10-25	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
Reaktionsmasse aus Ethylbenzol, m-, p-Xylol	01-2119555267-33	-	905-562-9	2.5-10	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2, Eye Irrit. 2, STOT SE 3, STOT RE 2, Asp. Tox. 1	H226,H312,H332,H315,H319,H335,H373,H304	Q
ethylbenzene	01-2119489370-35	100-41-4	202-849-4	<2	Flam. Liq. 2, Acute Tox. 4, STOT RE 2, Asp. Tox. 1, Aquatic Chronic 3	H225,H332,H373,H304,H412	A
2-methoxy-1-methylethyl acetate	01-2119475791-29	108-65-6	203-603-9	<2	Flam. Liq. 3, STOT SE 3	H226,H336	A
xylene	01-21194488216-32	1330-20-7	215-535-7	<1	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2, Eye Irrit. 2, STOT SE 3, STOT RE 2, Asp. Tox. 1	H226,H312,H332,H315,H319,H335,H373,H304	A,W
4-methylpentan-2-one; isobutyl methyl ketone	01-2119473980-30	108-10-1	203-550-1	<2.5	Flam. Liq. 2, Acute Tox. 4, Eye Irrit. 2, STOT SE 3	H225,H332,H319,H335	A

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting



Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

Skin contact : May cause irritation.
Symptoms : redness and pain
Eye contact : Irritating to eyes
Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8



Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Paints

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	200 ppm
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	20 ppm
		STEL	50 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, United Kingdom			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	125 ppm

Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	50 ppm
		STEL	100 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, Ireland			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	200 ppm
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	TWA	20 ppm
		STEL	50 ppm
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
xylene	1330-20-7	TWA	50 ppm
		STEL	100 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation Wear suitable protective gloves
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

6 / 11

Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : DME propelled liquid.
colour : See color cap.
odour : Characteristic odor.
pH : Not applicable.
Boiling point/range : Not available.
Flash point : - 41 °C
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0.778 g/cm³ (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : 240 °C
Viscosity : Not available.

9.2. Other information

VOC = volatile organic compounds 692 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO₂



Productname : ACRYLIC PAINT
 Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
 Replaces:

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	May cause irritation.
Eye contact :	Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	LD50 oral rat	2080 mg/kg
2-methoxy-1-methylethyl acetate	108-65-6	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	10.8 mg/l
		LD50 derm.rat	> 5000 mg/kg
		LD50 derm.rabit	> 5000 mg/kg
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
n-butyl acetate	123-86-4	LD50 oral rat	10760 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 1400 mg/kg
ethyl acetate	141-78-6	LD50 oral rat	5620 mg/kg
		LC50 inhal.rat	30 mg/l
		LD50 derm.rabit	> 20000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified



Productname : ACRYLIC PAINT
 Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
 Replaces:

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
4-methylpentan-2-one; isobutyl methyl ketone	108-10-1	LC50 fish	505 mg/l
2-methoxy-1-methylethyl acetate	108-65-6	LC50 fish	100-180 mg/l
		EC50 daphnia	> 400 mg/l
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
ethyl acetate	141-78-6	IC50 algae	5600 mg/l
		LC50 fish	230 mg/l
		EC50 daphnia	610 mg/l

12.2. Persistence and degradability

12.3. Bioaccumulative potential

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

GWP (global warming potential): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

Productname : ACRYLIC PAINT
Ref.Nr.: BDS002639_3_20201203 (EN)

Creationdate : 03.12.20 Version : 1.0
Replaces:

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H312 : Harmful in contact with skin.
H315 : Causes skin irritation.
H319 : Causes serious eye irritation.



Productname :	ACRYLIC PAINT	Creationdate :	03.12.20 Version : 1.0
Ref.Nr.:	BDS002639_3_20201203 (EN)	Replaces:	

H332 : Harmful if inhaled.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H373 : May cause damage to organs through prolonged or repeated exposure

H412 : Harmful to aquatic life with long lasting effects.

acronyms and synonyms:

TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistent bioaccumulative toxic
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.