Operating Manual Conductivity measuring instrument GLF 100 as of Version 0.3

CONTENTS

1		IN GENERAL	. 2
	1.1		. 2
	1.2		. 2
	1.3		
	1.4		
	1.5	5 Pushbuttons	. 2
2		GENERAL INFORMATION ABOUT CONDUCTIVITY MEASURING	. 3
	2.1		
	2.2		
	2.3		
	2.4		
	2.5	5 HOLD - FUNCTION	. 3
3		CONFIGURATION OF THE INSTRUMENT	. 4
4		ADJUSTING OF THE INSTRUMENT	. 5
5		SYSTEM MESSAGES	_
3			
6		INSPECTION OF THE ACCURACY / ADJUSTMENT SERVICES	. 5
7		SDECIEICATION	-

precise measurements of conductivity and TDS(total dissolved solids) and Salinity

Applications

- Sweet and seawater aquaristics
- Fish farming
- Drinking water monitoring etc.



In General

Safety Instructions

This device has been designed and tested in accordance to the safety regulations for electronic devices. However, its trouble-free operation and reliability cannot be guaranteed unless the standard safety measures and special safety advises given in this manual will be adhered to when using it.

- Trouble-free operation and reliability of the device can only be guaranteed if it is not subjected to any other climatic conditions than those stated under "Specification".
- Transporting the device from a cold to a warm environment condensation may result in a failure of the function. In such a case make sure the device temperature has adjusted to the ambient temperature before trying a new start-up.
- The circuitry has to be designed most carefully if the device should be connected to other devices. Internal connection in third party devices (e.g. connection GND and earth) may result in not-permissible voltages impairing or destroying the device or another device connected.
- Whenever there may be a risk whatsoever involved in running it, the device has to be switched off immediately and to be marked accordingly to avoid re-starting. Operator safety may be a risk if:
 - there is visible damage to the device or the device is not working as specified
 - the device has been stored under unsuitable conditions for a longer time In case of doubt, please return device to manufacturer for repair or maintenance.
- Warning: Do not use these product as safety or emergency stop device, or in any other application where failure of the product could result in personal injury or material damage. Failure to comply with these instructions could result in death or serious injury and material damage.

Operating And Maintenance

- If the symbol "LO BAT" is displayed at the left side of display, the battery is weak, measuring can be continued for a short period. If "bAt" is displayed in the main display the battery is used up and needs to be replaced. Measuring is no more possible.
- The battery has to be removed, when storing device above 50°C.


Hint: We recommend removing the battery if device is not used for a longer period of time! Risk of Leakage

- Treat device and probes carefully. Use only in accordance with above specification. (do not throw, hit against etc.). Protect from soiling, especially around the needles.
- After switching on the instrument a segment test (all segments) is displayed, followed by the measuring unit and, if activated, the auto power off function (please refer to configuration)

Disposal Notice

- Dispense exhausted batteries at destined gathering places.
- Send the device directly to us, if it should be disposed. We will dispose the device appropriate and non-polluting.

Display Elements



1. BAT 2. measurement display

3. unit arrows

4. nLF 5. HLD


Indicates low battery

consider additional arrows and symbols in

TDS-measurement in mg/l or conductivity measurement in µS/cm or mS/cm or Salinity Non linear temperature compensation is active

Measure value is 'frozen' (Key 3)

Pushbuttons



key 1: On/Off key

Press long: off;

Press short: Show temperature

key 2:

Choose between measuring value / min value / max value

press 2s: reset min and max value


Key 3: hold: Hold current measuring value ('HLD' in display)

2 General Information About Conductivity Measuring

2.1 The Conductivity Measuring Cell

During the measurement, the conductivity measuring cell must be dipped at least in so far, that at least 30mm beginning from the top of the measuring cell, is located in the medium.

The maximum immersion depth for continuous operation should not exceed 110mm.



The measuring cell can either be stored dry or in water. After dry storage wetting time will be prolonged slightly. If changing over from one liquid to another with conductivities varying widely make sure to properly rinse and shake dry measuring cell.

Attention: Measuring cell must never come into contact with water-repellent materials such as oil or silicone.

If conductivity measured is much higher or lower than expected this may be due to the electrode being soiled with non-conducting or conducting foreign materials. Measuring cell has to be cleaned with a watery soap solution. When measuring media with low conductivities the electrode has to be stirred sufficiently.

2.2 Measuring hints

Conductivity measuring is comparably easy to perform, the precision of the instrument is very constant if it is used as intended. Depending on the necessary accuracy the instruments can be used up to several years without recalibration of the cell constant.

If the accuracy should be controlled or improved, this is done by means of suitable reference solutions and the adjusting of the cell factor.

Attention! Wrong handling of reference solution can make them useless very fast.

Measuring procedure:

Especially when measuring low conductivity: Before immersion to the measuring solution, rinse the electrode with deionised water, dry with a paper towel and shake remaining water out.

The measuring is speeded up considerably, if the electrode is immersed and pulled out the solution several times.

Especially when measuring low conductivity the electrode needs sufficient flow during the measuring, e.g via stirring the solution.

When temperature compensation is activated, the electrode needs enough time to adjust to the actual temperature of the measuring solution to work accurate.

2.3 Temperature compensation

The conductivity of aqueous solution is temperature dependent. The dependency itself is strongly dependent on the kind of solution. For the most applications e.g. in fish farming etc., the non linear temperature compensation of natural waters is precise ("nLF" according to EN 27888). The most common reference temperature is 25°C.

2.4 Min-/max- value memory

The lowest and highest measured value since the turning-on of the device will be stored.

Watch MIN value (Lo): press shortly key **mode** once display changes between 'Lo' and MIN value Watch MAX value (Hi): press shortly **mode** once again current value: press shortly **mode** once again delete MIN/MAX value: press **mode** for 2 sec. MIN and MAX values will be deleted, the display shows shortly 'CLr' (clear)

After switching-off and turning-on again all min-/max- values will be deleted.


2.5 Hold - function

When the *hold* – key is pressed, the current measured value will be 'frozen' (display symbol: HLD) until the key is pressed again. Then the device will measure in its normal way again.

3 Configuration of the instrument

To configure the instruments according to Your needs proceed like follows::

- Switch off instrument.
- Switch on and press **mode-key during the segment test**), until the display shows the first parameter ,P_oF'
- If a parameter should be edited, press key up or down (), the setting of the parameter will be shown and can be changed via up/down keys.
- Jump to the next parameter with



Pressing unit

again stores the settings, the instruments restarts (segment test)

Please note: If there is no key pressed within the menu mode within 2 minutes, the configuration will be cancelled, the entered settings are lost!

Note for temperature compensation: To measure the TDS value always use non-linear temperature compensation for natural water (reference temperature = 25°C).

To measure salinity the instrument automatically switches over to the non-linear temperature compensation acc. to IOT (reference temperature = 15°C)..

Adjusting of the instrument

The cell correction may change due to natural ageing or deposits at the measuring cell. In case you have an accurate reference liquid, you may adjust the instrument by changing the cell constant accordingly. The temperature measuring is very stable and has to be adjusted in very seldom cases only.

To adjust the instruments according to Your needs proceed like follows::

- Switch off instrument.
- Switch on
-), the setting of the parameter will be shown If a parameter should be edited, press key up or down (and can be changed via up/down keys.
- Jump to the next parameter with key

parameter	value	meaning	
key on/off unit	keys mode hold		
ΓFII	Cell-constant		
	0.8001.200	Adjustment of the measuring cells cell-constant	
0F5.E	Offset of temperature		
U	-2.02.0°C -3.63.6°F	Offset setting of temperature measurement (see below)	
5[L.E	Scale of temperature		
J L L.L	-5.005.00%	Scale adjustment of temperature measurement Display = (measured value - offset) * (1 + scale adjustment/100)	



Pressing again stores the settings, the instruments restarts (segment test)

If there is no key pressed within the menu mode within 60 seconds, the adjusting will be cancelled, the entered settings are lost!

System Messages

- measuring range has been exceeded
- Sensor Error
- System fault the device has detected a system fault (defective or far outside allowable ambient Er. 7 =temperature range)

If "BAT" is displayed at the left side of display, the battery is weak, measuring can be continued for a short period. If "bAt" is displayed in the main display the battery is used up and needs to be replaced. Measuring is no more possible.

Inspection of the accuracy / Adjustment Services

Accuracy can be inspected with test-solutions (extra equipment).

If the precision is no more corresponding to the imprint of the GPAD 38, we suggest to send the device to the manufacturer for a new adjustment.

7 Specification

Measuring

Principle Conductivity measuring via 2 pole graphite electrode

Meas. Range Resolution

Conductivity $0 \dots 2000 \mu S/cm$ $1 \mu S/cm$

0.01 ... 20.00mS/cm 0.01mS/cm 0.1 ... 100.0mS/cm 0.1mS/cm

TDS 0 ... 1999 mg/l 1mg/l Salinity 0.0 ... 50.0 g/kg 0.1g/kg

Temperature -10.0 ... 110.0°C

Electrode 2 pole graphite electrode, integrated temperature sensor

Electrode material: special graphite

Dimensions: dia. 12mm, length 120mm, min immersion depth 30 mm

Cable length ca. 1.2m

Accuracy ±1Digit (at nominal-temperature)

Conductivity, TDS, Salinity: ±0.5% of m.v. ±0.5% FS

Temperature ±0.3K

T.-compensation: non-linear temperature compensation according to EN 27888, reference temperatures 20°C and 25°C

Nominal temperature 25°C

Ambient Temperature instrument -25 ... +50°C

Temperature cell -5 ... +80°C (short time 100°C)

Relative humidity instrument 0 ... 95%r.F. (non condensing)

Storage temperature -5 ... +50°C

Housing Dimension: 110 x 67 x 30 mm (L x B x D)

impact resistant ABS, membrane keyboard, transparent panel.

Front side IP65

Weight approx. 155 g

Power Supply 9V-Battery, type IEC 6F22 (included)

Power Consumption <1.5mA

Display ca. 11 mm high, 4-digit LCD-display with additional segments

Pushbuttons 3 membrane keys for on/off switch, menu operation, min/max/ hold-function etc.

Hold Function Press key to store current value.

Automatic-Off-Function Device will be automatically switched off if no key is pressed for the time of the power-off delay. The

power-off delay can be set to values between 1 and 120 min.; it can be completely deactivated.

EMC: The device corresponds to the essential protection ratings established in the Directives of the European

Parliament and of the council on the approximation of the laws of the member states relating to the

electromagnetic compatibility (2004/108/EC). EN61326 +A1 +A2 (Appendix B, class B),

additional error: < 1% FS