

Category IV for greater safety



Compact TRMS digital multimeters



- AC/DC current up to 10 A or 600 A with a current clamp giving direct readings
- High sensitivity with a resolution of 0.01 mV
- Their protection enables them to withstand overloads up to 8,000 V
- V_{LowZ} function to avoid the problem of disturbance voltages

IEC 61010
**600 V
CAT IV**

IEC 61010
**1,000 V
CAT III**


IP
54

The **C.A 5231** and **C.A 5233** multimeters are ideal for the needs of electrical installers, self-employed electricians and heating or air-conditioning specialists.

Compact and simple, they are exceptionally easy to read thanks to their large backlit display including a bargraph. Their built-in shockproof protection also makes them rugged instruments.

TECHNICAL SPECIFICATIONS

	C.A 5231	C.A 5233
Display	6,000-count backlit display + 61-segment bargraph	
Acquisition	True RMS	
Autorange or manual	Yes	
Bandwidth	3 kHz [V] / 1 kHz [A]	
Best accuracy	0.2 %	
AC voltage	6 calibres - 1,000 V - Resolution: 0.01 mV	6 calibres - 600 V - Resolution: 0.01 mV
AC LowZ voltage	4 calibres - 1,000 V - Resolution: 0.001 V	4 calibres - 600 V - Resolution: 0.001 V
DC voltage	6 calibres - 1,000 V - Resolution: 0.01 mV	6 calibres - 600 V - Resolution: 0.01 mV
AC current / DC current	With 1 mV/A clamp: 1 calibre - 600 A Resolution: 0.1 A	2 calibres - 10 A Resolution: 0.001 A
Resistance measurement	6 calibres - 60 MΩ - Resolution: 0.1 Ω	
Audible continuity / Diode test	Yes / Yes	
Frequency / Duty ratio		3 calibres: up to 3 kHz / Yes
Capacitance	6 calibres - 1,000 μF - Resolution: 0.01 nF	
Temperature (with external K thermocouple)		1 calibre -20 °C to +760 °C / -4 °F to +1,400 °F Resolution: 1°
No-contact voltage detection (NCV)	Yes	
Display Hold function	Yes	
Relative mode		Yes
Min-Max		Yes
Power supply	9 V alkaline battery (6LF22)	
Leakproofing	IP54	
Dimensions	155 x 75 x 75 mm	
Weight	320 g	
Electrical safety (IEC 61010)	600 V CAT IV / 1,000 V CAT III	600 V CAT IV / 600 V CAT III



TO ORDER:

- C.A 5231:**
delivered with 2 measurement leads equipped with test probes,
a 9 V alkaline battery and an operating manual
in 5 languages> P01196731
- C.A 5233:**
same as the C.A 5231 with temperature sensor
and adapter> P01196733
- C.A 5231+MINI03:**
C.A 5231 delivered with MINI 03
current clamp (100 A AC)> P01196734

ACCESSORIES

- C.A 1871 infrared probe for multimeter> P01651610Z
C.A 801 single-channel temperature adapter> P01652401Z
C.A 803 two-channel temperature adapter
with differential measurement> P01652411Z
Multi-position DMM mounting accessory> P01102100Z

For the C.A 5233

- CMI214S current measurement lead> P03295509
Adapter for K thermocouple
(delivered 1 wire thermocouple)> P06239306
HRC fuse, 6 x 32, 10 A 600 V 50 kA> AT0084

For the C.A 5231

- 100 A 1,000/1 AC current clamp MINI03 model> P01105103Z
600 A AC/DC current clamp PAC10 model> P01120070



FRANCE
Chauvin Arnoux
190, rue Championnet
75876 PARIS Cedex 18
Tel: +33 1 44 85 44 38
Fax: +33 1 46 27 95 59
export@chauvin-arnoux.fr
www.chauvin-arnoux.fr

UNITED KINGDOM
Chauvin Arnoux Ltd
Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
Dewsbury, West Yorkshire - WF12 7TH
Tel: +44 1924 460 494
Fax: +44 1924 455 328
info@chauvin-arnoux.co.uk
www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
P.O. BOX 60-154
1241 2020 JAL EL DIB - LEBANON
Tel: +961 1 890 425
Fax: +961 1 890 424
camie@chauvin-arnoux.com
www.chauvin-arnoux.com

**CHAUVIN
ARNOUX**
GROUP