

KERN GAB12K0.1N

Kontroll- und Portionierwaage, auch mit Eichzulassung [M]



Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readout [d]:	100 mg
Recommended adjusting weight:	12 kg (F2)
Reproducibility:	100 mg
Resolution:	120000
Stabilisation time:	2 s
Tare range:	-12000000 mg
Warm up time:	2 h
Weighing range [Max]:	12 kg
Weighing system:	Strain gauge
Weighing units:	g kg

Display

Display digit height:	2,400 cm
-----------------------	----------

Counting

Counting resolution:	120000
Minimum piece weight at piece counting (Laboratory):	100 mg
Minimum piece weight at piece counting (Normal):	1 g

Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	90 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

DAkKS Certificate:	963-128
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	450 x 380 x 210 mm
Gross weight:	4,200 kg
Net weight:	3 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	320 x 330 x 125 mm
Dimensions of display device (WxDxH):	320 x 350 x 125 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	294 x 225 mm