






Analogue Panel Meter

HN96 Series



Panel cut-hole



unit: mm±1

Model	HN96-5A	HN96-25A	HN96-25V	HN96-300V	HN96-500V	HN96-F
Meter Type	AC Ameter		AC Voltmeter			Frequency meter
Measuring area	5A	25A	25V	300V	500V	45~55Hz /380V max.
Instruments	Moving Iron	Moving Iron	Moving coil	Moving coil	Moving coil	Moving coil
Accuracy class	1.5					
Operating Temp.	-25°C ~ 55°C					
Operating Humidity	20-95% RH					
Storage Temp.	-40°C ~ 70°C					
Storage Humidity	20-95% RH					
Product Weight	approx. 170g					