



Discover more details and matching accessories online!

Advanced features for demanding applications

Features

- **1** Impact (rebound) sensor: The bounce module is accelerated by a spring against the item being tested. Depending on how hard the object is, the kinetic energy of the module will be absorbed. The speed reduction will be measured and converted to Leeb hardness values
- External impact sensor (Type D) included
- High levels of mobility and flexibility in comparison with stationary table-top devices and hardness testing devices with internal sensors
- All measurement directions possible (360°) thanks to an automatic compensation function
- **2** Hardness test block for calibration included (790 ± 40 HL)
- Internal memory for up to 9 measurement values

- Mini statistics function: displays the measured result, the average value, the impact direction, date and time
- SAUTER HMM: Infrared printer for direct output of the measuring results is included with delivery
- SAUTER HMM-NP: identical product features as the SAUTER HMM model, but comes without the printer
- Measurement value display: (B and C), Vickers (HV), Brinell (HB), Shore (HSD), Leeb (HL), tensile strength (MPa)
- Automatic unit conversion: The measuring result is automatically converted into all specified hardness units
- **3** Delivered in a robust carrying case

Technical data

- Precision: ± 1 % at 800 HLD (± 6 HLD)
- Measuring range tensile strength: 375–2639 MPa (steel)
- Minimum sample weight on a solid and stable support: 2 kg with fixed coupling
- Minimum sample material thickness: 3 mm with coupling on fixed base
- Minimum sample radius (concave/convex): 50 mm (with support ring: 10 mm)
- Batteries included, 3×1.5 V AAA, operating time up to 30 h, AUTO-OFF-function to preserve the battery
- SAUTER HMM: External mains adapter for printer, as standard
- Overall dimensions W×D×H 150×80×30 mm

STANDARD

HMM

OPTION

Model	Sensor	Measuring range	Readout	Net weight	Option
					Factory calibration certificate
SAUTER		HL	[d] HL	approx. kg	KERN
HMM	D	170 – 960	1	0,25	96 1-13 1
HMM-NP	D	170 – 960	1	0,25	96 1-13 1