

KERN CH50K50

Praktisch, preiswert und stets griffbereit

KERN®



Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	20 h
-----------------	------

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128H

Category

Brand:	KERN
Category:	Balances
Product Group:	Hanging scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	225 x 155 x 72 mm
Gross weight:	540 g
Net weight:	316 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	90 x 30 x 176,5 mm
Overall dimensions mounted (WxDxH):	90 x 30 x 280 mm

Measuring system

Linearity:	100 g
Precision (of [Max]):	0,005
Readout [d]:	50 g
Recommended adjusting weight:	20 kg (M3)
Reproducibility:	50 g
Resolution:	1000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	50 kg
Weighing system:	Strain gauge
Weighing units:	kg lb N

Display

Display digit height:	1,100 cm
-----------------------	----------