
Setpoint adjuster

LED setpoint adjuster | **Standard signal output for mA or V, also time-controlled (DC)** | **Codix 533**



The Codix 533 setpoint adjuster provides a standard signal or a freely programmable, time-controlled signal sequence of 0 to 12 V or 0 to 24 mA.

The setpoint adjuster is a real innovation that opens up new applications in process technology and automation.



Innovative

- Function of a digital time controller with analog output.
- Manual functions with direct input or stepped incremental output of the setpoint.
- 4-digit, 8 mm high top-quality LED display.
- Physical variables output / 0 ... 12 V or 0 ... 24 mA analog signals.
- Units of display can be freely programmed and displayed – no conversion of the specified output value required.
- Ideal for simulation runs without the need for expensive, time-consuming running-in of processes.

Powerful

- Simpler to run processes than with a PLC or process controller.
- Everything can be programmed easily by means of 2 keys and the text menu.
- Digital setting - no additional DIP switches or potentiometers.
- Display allows simple monitoring of the specified setpoint output.
- User-friendly display form as direct digital value.
- 3 separate functions integrated as standard in the Codix 533.
- High accuracy of < 0.2% of the final value.

Order no.

Setpoint adjuster **6.533.012.300**


Delivery specification

- Setpoint adjuster
- Mounting clip
- Gasket
- Front bezel for screw mounting (T008181) 56 x 40 mm [2.20 x 1.57"], panel cut-out 50 x 25 mm [1.97 x 0.98"]
- Front bezel for clip mounting (T008180) 53 x 28 mm [2.09 x 1.10"], panel cut-out 50 x 25 mm [1.97 x 0.98"]
- 1 set of self-adhesive symbols
- Instruction manual, multilingual

© Fritz Kübler GmbH, subject to errors and changes. 02/2024

LED setpoint adjuster | Standard signal output for mA or V, also time-controlled (DC) | Codix 533

Accessories / Mounting examples



		Type / size	Description		Order no.	suitable gasket
Adapter front bezel		**53 x 28 mm [2.09 x 1.10“]**	for cut-out 50 x 25 mm [1.97 x 0.98“] to cut-out 45 x 22.2 mm [1.77 x 0.94“]	black anthracite	**T008165** **T008180**	**N511015**
		**56 x 40 mm [2.20 x 1.57“]**	for cut-out 50 x 25 mm [1.97 x 0.98“] to cut-out 45 x 22.2 mm [1.77 x 0.94“] screw mounting	black anthracite	**T008161** **T008181**	**N511045**
		**72 x 36 mm [2.83 x 1.42“]**	for cut-out 68 x 33 mm [2.68 x 1.30“] to cut-out 45 x 22.2 mm [1.77 x 0.94“]	black and silver anodised as set	**162704Set**	–
		**60 x 50 mm [2.36 x 1.97“]**	for cut-out 54 x 29 mm [2.13 x 1.14“] to cut-out 45 x 22.2 mm [1.77 x 0.94“] screw mounting	black	**N003001**	**N511005**
		**48 x 48 mm [1.89 x 1.89“]**	for cut-out 45 x 45 mm [1.77 x 1.77“] to cut-out 45 x 22.2 mm [1.77 x 0.94“]	black	**T008883**	–
Sealing cover IP65		**K1**	only in conjuction with adapter front bezel 60 x 50 mm N003001	transparent / grey transparent / black	**G008300** **G008301**	–
Transparent cover IP65		**1 Dv** (mounted on bezel)	cover lockable, for cut-out 54 x 29 mm [2.13 x 1.14“], only in conjuction with adapter front bezel 60 x 50 mm N003001	transparent / black	**N003002**	**N511019**
Gasket counter			48 x 24 mm (for installation in adapter front bezel) 49 x 25 mm		**N511029** **N511034**	
Mounting frame		**cut-out 50 x 25 mm [1.97 x 0.98“]**	via adapter T008180 for snap-on mounting on 35 mm [1.38“] top-hat DIN rail	chromated	**G300004**	–
Enclosure blind		**48 x 24 mm [1.89 x 0.94“]**	for cut-out 45 x 22.2 mm [1.77 x 0.94“] and cut-out 50 x 25 mm [1.97 x 0.98“]	anthracite	**G003836**	–

incl. in delivery

© Fritz Kübler GmbH, subject to errors and changes. 02/2024

LED setpoint adjuster | Standard signal output for mA or V, also time-controlled (DC) | Codix 533

Technical data

General technical data

Display	4 digits, red 7 segment LED display; 8 mm [0.32“] high
Data backup	EEPROM
Operating temperature	-20 °C ... +65 °C [-4°F ... +149°F] (non-condensing)
Storage temperature	-25 °C ... +85 °C [-13°F ... +185°F]

Electrical characteristics

Supply voltage	10 ... 30 V DC, galvanically isolated with integrated reverse polarity protection
Power consumption	max. 1 W
Test voltage	500 V, 50 Hz, 1 min.

Mechanical characteristics

Housing	front panel mount 48 x 24 mm [1.89 x 0.94“] acc. to DIN 43700; RAL 7021, dark grey
Protection	IP65 (front side)
Weight	approx. 50 g [1.76 oz]
Connections	screw terminal, pitch 5.08 mm [2“], 7 pin

Standard signal outputs / control input

Current output		0 ... 24 mA, increment 10 µA
	load	20 mA: ≤ 500 Ohm > 20 mA: ≤ 400 Ohm
Voltage output		0 ... 12 V, increment 10 mV
	load	≥ 2 kOhm
Control input Hold (HIGH active)	HIGH	4 ... 30 V DC
	LOW	0 ... 2 V DC
Accuracy		< 0.2% of the full scale value ±0.02 %/$K_{Ambient}$

Approvals

UL compliant in accordance with	File no. E128604
CE compliant in accordance with	
EMC Directive	2014/30/EU
RoHS Directive	2011/65/EU

3 operating modes programmable

Manual direct input (Setp)

- Fast adjustment and manual approach to the desired setpoint value.
- Setpoint value can be specified directly during operation via the keys in V or mA.
- Output of the value 3 seconds after the last key actuation.


Manual ramping function (Man)

- Possibility of a stepped, incremental approach to the desired setpoint value using the keys on the front.
- Input of the minimum and maximum setpoint values and the increment by key actuation in the programming level.
- During operation the device starts with the minimum setpoint value – the right key is used to increase the value by the amount of the increment; the left key decreases the value.
- The programmed maximum value cannot be exceeded.

Automatic ramping function (Auto)

- Function of a digital time based controller with analog output. Setpoint values can be programmed and carried out for process sequences, either cyclic or time dependent: irrigating, dosing, lubricating, filling, venting, mixing.
- With max. 20 current or voltage values.
- Cyclically limited (time) or unlimited.

Example of an automatic ramping function




Example with 8 points	
ou. 1	0 V
PE 1	5 s
ou.2	3 V
PE 2	5 s
ou. 3	2 V
PE 3	10 s
ou. 4	3 V
PE 4	10 s
ou. 5	3 V
PE 5	10 s
ou. 6	8 V
PE 6	10 s
ou. 7	8 V
PE 7	10 s
ou. 8	0 V
PE 8	5 s

© Fritz Kübler GmbH, subject to errors and changes. 02/2024

LED setpoint adjuster | Standard signal output for mA or V, also time-controlled (DC) | Codix 533

Block diagram



Inputs

1	2	3	4
10 ... 30 V DC	GND_1	GND_2	Hold

Outputs

5	6	7
0 ... 24 mA (Iout)	GND_3	0 ... 12 V DC Uout)


Terminal assignment

Inputs

1	2	3	4
10 ... 30 V DC	GND_1	GND_2	Hold

Outputs

5	6	7
0 ... 24 mA	Analog GND_3	0 ... 12 V DC




1 Supply voltage
2 Analog input

© Fritz Kübler GmbH, subject to errors and changes. 02/2024


LED setpoint adjuster | **Standard signal output for mA or V, also time-controlled (DC)** | **Codix 533**

Dimensions

Dimensions in mm [inch]



Front bezel







1 Countersinking Af3, DIN 74

© Fritz Kübler GmbH, subject to errors and changes. 02/2024

LED setpoint adjuster | Standard signal output for mA or V, also time-controlled (DC) | Codix 533

Areas of application / Applications

	Simple control (fixed installation) in plants, machines and devices	For use in set-up mode of plants, machines and devices
	Time-based ramping up or down of:	Manual (direct) specification or time-based or manual setting (ramping up or down) of:
	Rotary speeds (e.g. frequency converter), flow rates, temperatures, positions, pressure and fill levels. In short: all physical quantities that can be represented with analog standard signals.	
Applications	Simple time controller with standard signal output	
	Commissioning, running-in processes or rotary speed control of motors through setpoint setting.	Calibration of filling levels and flow rates: the setpoint adjuster simulates the output signals of a level or flow sensor for configuring a control.
		
	Control of simple, time-based processes by means of an analog signal, e.g. ramping control for locks and sluices	Alignment for temperature-based processes without having to heat up the plant: the setpoint adjuster can simulate various processes for test purposes.
		
Solution with different modes	2 operating modes are provided for that purpose: - Manual ramping function - Automatic ramping function	The following operating modes are provided for that purpose: - Manual direct input - Manual ramping function - Automatic ramping function
Advantages	Instead of using an expensive, complex and difficult-to-use PLC, our setpoint adjuster can handle this task as a standalone device. The user saves costs and the task can be performed in a flexible and quick way, even without any prior knowledge.	The setpoint adjuster simulates the sensor signal that is read by the physical process, e.g. the rise of the temperature, the filling of tank plants. Expensive and complex running-in of processes can be replaced with the simulation performed by the setpoint adjuster.
	The output signal can be displayed directly or scaled in any desired unit. The user always sees the exact progress. An easy-to-use device with three selectable modes is available.	

© Fritz Kübler GmbH, subject to errors and changes. 02/2024