


SAUTER AC 12

Universal 2-jaw grip for tension and rupture tests

KERN



Pictograms

STANDARD



Category

Brand	Sauter
Product category	Clamp
Product group	Screw tension clamp

Construction

Dimensions completely mounted (W×D×H)	110×80×25 mm
Material	steel
Material housing	metal
Mounting - force dissipation	External thread M10
Maximum clamp width	25 mm
Clamping width	5 mm
Tensile/compressive force [Max]	5 kN

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	150×100×10 mm
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	1,00 kg
Shipping weight	0,98 kg

Product information

GTIN/EAN number	4045761122352
REACH classification	no prohibited substances