



Discover more details and matching accessories online!

Pallet truck scale with complete protection against dust and water splashes IP65/67 and a memory for a container weight

Features

- PRE-TARE function for manual subtraction of a known container weight, useful for checking fill-levels
- **1** Display device: Plastic, protected against dust and water splashes IP65
- **2** Load fork: Protection against dust and water splashes IP67, temporary use in wet areas possible
- Pivot range 206°
- Castors: Solid rubber on aluminium rims
- **3** Load rollers: Tandem tyres to overcome thresholds and obstacles more easily
- Summation of weight values

Technical data

- Large LCD display, digit height 28 mm
- Ready for use: Batteries standard, 4×1.5 V AA, operating time approx. 80 h
- Permissible ambient temperature -10 °C/40 °C

Shipment via freight forwarder. Please ask for dimensions, gross weight, shipping costs

STANDARD

1 **2**

OPTION

Model	Weighing capacity	Readability	Linearity	Net weight	Options
					Calibr. Certificate
	[Max] kg	[d] kg	kg	approx. kg	DAkkS accr. KERN
KERN VHB 2T1	2000	1	± 2	110	963-131