



Discover more details and matching accessories online!

Robust, compact hanging scale with high level of protection against dust and water spray

Features

- **1** With the TÜV certification mark, the scales meet the requirements of the standard EN 13155 (Non-fixed load lifting attachments/ Breakage resistance) and EN 61010-1 (Electrical safety)
- **2** Housing stainless steel, IP65-protected against dust and water splashes
- Ideal for rapid control in goods-in and goods-out
- Also essential in the private sector to determine the weight of fish, game, fruits, bicycle parts, suitcases etc.
- Hold function: For easy reading of the weighing result, the display can be „frozen“ in different ways. Either automatically when the weighing value remains unchanged or manually by pressing the Hold key
- Peak load display (peak hold)
- Internal measuring frequency: 5 Hz
- Snap link (stainless steel) with safety catch as standard
- Hook (stainless steel) as standard

Technical data

- LCD display, digit height 12 mm
- **3** Second display on the back of the balance
- Hole diameter of load support ca. 14 mm
- Ready for use: Batteries included, 2×1.5 V AA, operating time up to 300 h
- Weighing units: kg, lb, N
- Overall dimensions W×D×H 96×48×179 mm
- Net weight approx. 0,50 kg
- Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



Model	Weighing capacity	Readability	Options
			Calibr. Certificate
KERN	[Max] kg	[d] g	DAkkS accr. KERN
HCN 50K100IP	50	100	963-128H
HCN 100K200IP	100	200	963-129H
HCN 200K500IP	200	500	963-129H