


# Linear measuring technology

**Draw wire mechanics with analog sensor**

**Draw wire encoder A40, 1 m  
Draw wire encoder A41, 2 m**

**Measuring length max. 2 m  
Traverse speed max. 1 m/s**



The draw wire encoders A40 and A41 with analog output is characterized by its compact design. They are available with a potentiometer, voltage or current output.



Analog output

### Compact and simple

- Measuring length up to 2000 mm.
- For applications with a low traversing speed.
- Easy to install.

**Order code draw wire encoder**

**D5.350X.AXX.X.0000**  
Type    a    b    c

**a** Measuring range

- 1 = 1000 mm
- 2 = 2000 mm

**b** Output circuit

- 11 = analog output 4 ... 20 mA
- 22 = analog output 0 ... 10 V DC power supply 15 ... 28 V DC
- 33 = potentiometer output 10 kΩ

**c** Type of connection


- 1 = cable 2 m [6.56'] for measuring range 1000 mm: axial for measuring range 2000 mm: radial
- 2 = radial M12 connector, 4-pin (only available for measuring range 2000 mm)

### Accessories for draw wire encoder

Dimensions in mm [inch]

Order no.

#### Guide pulley



Technical data:


- mounting bracket (anodized alum.)
- guide pulley (plastic POM)
- ball bearing (type 696-2R5)

Scope of delivery:

- 2 x countersunk screws for lateral fixing
- 2 x hexagonal screws for fixing on a flat surface

**8.0000.7000.0045**

#### Extension cable



Steel wire 2 m [6.56']

**8.0000.7000.0033**

Steel wire 5 m [16.40']

**8.0000.7000.0034**

Steel wire 10 m [32.81']

**8.0000.7000.0035**

Paraleine 2 m [6.56']

**8.0000.7000.0032**

# Linear measuring technology

<b>Draw wire mechanics with analog sensor</b>	<b>Draw wire encoder A40, 1 m</b> <b>Draw wire encoder A41, 2 m</b>	<b>Measuring length max. 2 m</b> <b>Traverse speed max. 1 m/s</b>
-----------------------------------------------	------------------------------------------------------------------------	----------------------------------------------------------------------




## Technical data

Mechanical characteristics (draw wire mechanics)		
<b>Measuring range</b>	<b>1000 mm (A40)</b>	<b>2000 mm (A41)</b>
<b>Speed max.</b>	0.8 m/s	1 m/s
<b>Working temperature</b>	0°C ... 50°C [+32°F ... +122°F]	-10°C ... +80°C [+14°F ... +176°F]
<b>Protection (sensor) acc. to EN 60529</b>	IP50	IP65
<b>Weight</b>	approx. 200 g [7.06 oz]	approx. 320 g [11.29 oz]
<b>Extension force <math>F_{min}</math></b>	2 N	
<b>Repeat accuracy</b>	±0.15 mm	
<b>Linearity</b>	±0.35 %	
<b>Material</b>	housing: plastic / zinc die-cast	wire: stainless-steel $\varnothing$ 0.45 mm plastic-coated

Electrical characteristics			
<b>Analog output</b>	0 ... 10 V	4 ... 20 mA	potentiometer 10 k $\Omega$
<b>Power supply</b>	15 ... 28 V DC	–	–
<b>Operating range</b>	–	15 ... 28 V DC	max. 48 V DC
<b>Temperature range</b>	0°C ... 50°C [+32°F ... +122°F]	0°C ... 50°C [+32°F ... +122°F]	0°C ... 50°C [+32°F ... +122°F]
<b>Load</b>	max. 500 $\Omega$	max. 500 $\Omega$	–
<b>CE compliant acc. to</b>	EMC guideline 2014/30/EU RoHS guideline 2011/65/EU		

### Terminal assignment


Color	BN	WH	GN	
Pin M12	1	2	3	4
0 ... 10 V	+ 24 V DC	0 V	$U_{out}$	n.c.
0 ... 20 mA	I+	I-	n.c.	n.c.
Potentiometer	Po	Pe	S	n.c.



### Dimensions

Dimensions in mm [inch]


#### for measuring range 1000 mm



1 2 x M4, max. screw-in depth 8 mm [0.32"]

#### for measuring range 2000 mm

##### cable connection



##### M12 connector

