

KERN VHB2T1



Wiegehubwagen mit komplettem Staub- und Spritzwasserschutz IP65/67 und Speicherplatz für ein Behältergewicht



Category

Brand:	KERN
Category:	Balances
Product Group:	Pallet truck scale

Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1600 x 560 x 1220 mm
Gross weight:	109 kg
Net weight:	106 kg
Shipping method:	Freight forwarder

Construction

Casing material:	Plastic
Overall dimensions mounted (WxDxH):	1550 x 555 x 1220 mm

Measuring system

Adjustment options:	External calibration
Linearity:	2 kg
Readout [d]:	1 kg
Recommended adjusting weight:	1500 kg (M2)
Reproducibility:	1 kg
Resolution:	2000
Stabilisation time:	3 s
Warm up time:	10 min
Weighing range [Max]:	2 t
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,800 cm
-----------------------	----------

Functions

PRE-TARE function:	yes
--------------------	-----

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

Power supply

Operating time:	80 h
-----------------	------

Service

Adjustment at the location of installation: 961-251

DAkkS Certificate:	963-131
--------------------	---------