## Kingbright

### 8.89mmx8.89mm LED LIGHT BAR

P/N: KB-2855SGD

SUPER BRIGHT GREEN


#### Features


•UNIFORM LIGHT EMITTING AREA.
•EASILY MOUNTED ON P.C. BOARDS.
•FLUSH MOUNTABLE.
•EXCELLENT ON/OFF CONTRAST.
•CAN BE USED WITH PANELS AND LEGEND MOUNTS.
•RoHS COMPLIANT.


#### Description

The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

### Package Dimensions & Internal Circuit Diagram







Notes:

1. All dimensions are in millimeters (inches), Tolerance is  $\pm 0.25(0.01")$  unless otherwise noted.

2. Specifications are subject to change without notice.

REV NO: V.7 CHECKED: Joe Lee

DATE: NOV/19/2005 DRAWN: Y.L.LI

## **Kingbright**

Selection Guide							
Part No.	Dice	Lens Type	lv (mcd) @ 20mA				
			Min.	Тур.			
KB-2855SGD	SUPER BRIGHT GREEN (GaP)	GREEN DIFFUSED	18	80			

#### Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Green	565		nm	IF=20mA
λD	Dominant Wavelength	Super Bright Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Green	30		nm	IF=20mA
С	Capacitance	Super Bright Green	15		pF	VF=0V;f=1MHz
Vf	Forward Voltage	Super Bright Green	2.2	2.5	V	IF=20mA
IR	Reverse Current	Super Bright Green		10	uA	VR = 5V


### Absolute Maximum Ratings at TA=25°C

Parameter	Super Bright Green	Units		
Power dissipation	105	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Dperating/Storage Temperature -40°C To +85°C				
Lead Solder Temperature [2]	260°C For 5 Seconds			

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.

# Kingbright



REV NO: V.7 CHECKED: Joe Lee DATE: NOV/19/2005 DRAWN: Y.L.LI