

Datasheet

Item no. 140416/ 140419 /140427/ 140426/ 140425/
140428/ 140421/ 140420/ 140424

V1_0717_01_en

Pilot Lamp









Product Overview

This series pilot lamp only use LED lamp as the light source. The advantage have: long life, gentle weight, small cubag, save energy. It is the advanced product of all kinds of the incandescence lamp and the neon lamp of the XD type. The cover of the lamp is made of PC material, and have good shock resistance. It can be used as indication pilot light, accident signal and other signals in the circuits of such equipment as telecommunication.

Specifications

- ⊙ Electrical Life ≥ 30000 hours
- ⊙ Permitted Voltage $\pm 20\%$ ($\geq 110V$)
- ⊙ Dielectric Strength: $2.5kV(AC\ RMS)$, $1\ min$
- ⊙ Usage Frequency (AC): $50 \sim 60Hz$
- ⊙ Rated Operating Current: $\leq 20mA$
- ⊙ Brightness: $\geq 100cd/m^2$
- ⊙ Comparative Tracking Index $CT1 \geq 100$, flame retardant
- ⊙ Insulation Resistance: $U_i \leq 60V, 5M\Omega$; $60V < U_i \leq 660V, 50M\Omega$
- ⊙ Light Color: red, green, yellow, white, blue, orange
- ⊙ Operating Temperature: $-25^\circ C \sim 55^\circ C$

Diagram of Interior Connection

| | AC/DC Type Pilot Lamp | AC Type Pilot Lamp | AC/DC Type Dual-color Lamp | AC Type Dual-color Lamp |
|------------------------|---|---|---|--|
| Normal Type |  |  |  Red: X1-X0 Green: X2-X0 (Yellow: X1-X2) |  Red: X1-X0 Green: X2-X0 |
| Anti-interference Type |  |  |  Red: X1-X0 Green: X2-X0 (Yellow: X1-X2) |  Red: X1-X0 Green: X2-X0 |

Note: 1, AC/DC type pilot lamp is resistor step-down form; AC type pilot lamp is capacitor step-down form.

2, When voltage is 110V or above it, The temperature of outer shell of AC/DC type pilot lamp is higher than AC type pilot lamp.

Attentions

- 1, The frequency of AC type pilot lamp is 50~60Hz. If work in other frequency ranges, it will be broken.
- 2, The common threshold value of anti-interference pilot lamp is below 40V; and if you need higher threshold value please tell us.

If you need to weld, please finish it in 3 seconds by the electric iron which is below 30W and don't exert external force on terminals. We suggest that the threshold value shouldn't be too high. Please check the routing if the interference voltage is too high.

3, Connection error is not allowable to AC type dual-color light, otherwise pilot lamp will be broken.



4, Avoid using welding mode to connect lines as possible and you should using general plug (2.5 x 0.8mm) to connect and wear the protective sleeve.

Datasheet

Item no. 140416/ 140419 /140427/ 140426/ 140425/
140428/ 140421/ 140420/ 140424

V1_0717_01_en

Pilot Lamp

| Shape | Color | Operating Voltage | Shape & Dimensions | Remarks |
|------------------|---|---|--|--|
| super short type |  | AC/DC 6V AC/DC 12V AC/DC 24V AC/DC 36V AC/DC 48V AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V |  | <ul style="list-style-type: none"> ⊙ Screw Type Connection ⊙ Electric Shock Protection Structure |

140416 : Signal lamp, 12V/DC, dia 22mm, red

140419 : Signal lamp, 12V/DC, dia 22mm, white

140427 : Signal lamp, 230V/50Hz, dia 22mm, blue

140426 : Signal lamp, 230V/50Hz, dia 22mm, green

140425 : Signal lamp, 230V/50Hz, dia 22mm, red

140428 : Signal lamp, 230V/50Hz, dia 22mm, white

140421 : Signal lamp, 24V/DC, dia 22mm, green

140420 : Signal lamp, 24V/DC, dia 22mm, red

140424 : Signal lamp, 24V/DC, dia 22mm, white

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.