

# BD677/A/679/A/681 BD678/A/680/A/682

# COMPLEMENTARY SILICON POWER DARLINGTON TRANSISTORS

- STMicroelectronics PREFERRED SALESTYPES
- COMPLEMENTARY PNP NPN DEVICES
- MONOLITHIC DARLINGTON CONFIGURATION
- INTEGRATED ANTIPARALLEL COLLECTOR-EMITTER DIODE

#### **APPLICATION**


 LINEAR AND SWITCHING INDUSTRIAL EQUIPMENT


#### DESCRIPTION

The BD677, BD677A, BD679, BD679A and BD681 are silicon epitaxial-base NPN power transistors in monolithic Darlington configuration mounted in Jedec SOT-32 plastic package.

They are intended for use in medium power linar and switching applications

The complementary PNP types are BD678, BD678A, BD680, BD680A and BD682 respectively.





Symbol	Parameter		Unit			
		NPN	BD677/A	BD679/A	BD681	1
		PNP	BD678/A	BD680/A	BD682	1
V <sub>СВО</sub>	Collector-Base Voltage (I <sub>E</sub> = 0)		60	80	100	V
V <sub>CEO</sub>	Collector-Emitter Voltage $(I_B = 0)$		60	80	100	V
V <sub>EBO</sub>	Emitter-Base Voltage (I <sub>C</sub> = 0)		5			V
lc	Collector Current		4			A
I <sub>CM</sub>	Collector Peak Current		6			A
Ι <sub>Β</sub>	Base Current		0.1			A
Ptot	Total Dissipation at $T_c \le 25$ °C		40			W
T <sub>stg</sub>	Storage Temperature		-65 to 150			°C
Tj	Max. Operating Junction Temperature		150			°C

ABSOLUTE MAXIMUM RATINGS

For PNP types voltage and current values are negative.

December 2000

### THERMAL DATA


R <sub>thj-case</sub>	Thermal Resistance Junction-case	Max	3.12	°C/W
R <sub>thj-amb</sub>	Thermal Resistance Junction-ambient	Max	100	°C/W

## **ELECTRICAL CHARACTERISTICS** (T<sub>case</sub> = 25 °C unless otherwise specified)


Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
I <sub>СВО</sub>	Collector Cut-off Current ( $I_E = 0$ )	$V_{CE}$ = rated $V_{CBO}$ $V_{CE}$ = rated $V_{CBO}$ $T_{C}$ = 100 °C			0.2 2	mA mA
I <sub>CEO</sub>	Collector Cut-off Current ( $I_B = 0$ )	$V_{CE}$ = half rated $V_{CEO}$			0.5	mA
I <sub>EBO</sub>	Emitter Cut-off Current $(I_C = 0)$	$V_{EB} = 5 V$			2	mA
$V_{CEO(sus)^*}$	Collector-Emitter Sustaining Voltage	I <sub>C</sub> = 50 mA for <b>BD677/677A/678/678A</b> for <b>BD679/679A/680/680A</b> for <b>BD681/682</b>	60 80 100			V V V
V <sub>CE(sat)</sub> *	Collector-Emitter Saturation Voltage	for <b>BD677/678/679/680/681/682</b> $I_{C} = 1.5 \text{ A}$ $I_{B} = 30 \text{ mA}$ for <b>BD677A/678A/679A/680A</b> $I_{C} = 2 \text{ A}$ $I_{B} = 40 \text{ mA}$			2.5 2.8	V V
V <sub>BE</sub> *	Base-Emitter Voltage	for <b>BD677/678/679/680/681/682</b> $I_C = 1.5 A$ $V_{CE} = 3 V$ for <b>BD677A/678A/679A/680A</b> $I_C = 2 A$ $V_{CE} = 3 V$			2.5 2.5	V V
h <sub>FE</sub> *	DC Current Gain	for <b>BD677/678/679/680/681/682</b> $I_C = 1.5 A$ $V_{CE} = 3 V$ for <b>BD677A/678A/679A/680A</b> $I_C = 2 A$ $V_{CE} = 3 V$	750 750			
h <sub>fe</sub>	Small Signal Current Gain	I <sub>C</sub> = 1.5 A V <sub>CE</sub> = 3 V f = 1MHz	1			

\* Pulsed: Pulse duration = 300 ms, duty cycle 1.5 %


### Safe Operating Areas




Derating Curve




### DC Current Gain (NPN type)




Collector-Emitter Saturation Voltage (NPN type)




Base-Emitter Saturation Voltage (NPN type)




DC Current Gain (PNP type)




Collector-Emitter Saturation Voltage (PNP type)




Base-Emitter Saturation Voltage (PNP type)






Base-Emitter On Voltage (NPN type)


Freewheel Diode Forward Voltage (NPN types)



Base-Emitter On Voltage (PNP type)




Freewheel Diode Forward Voltage (PNP types)



DIM.	mm			inch			
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
А	7.4		7.8	0.291		0.307	
В	10.5		10.8	0.413		0.445	
b	0.7		0.9	0.028		0.035	
b1	0.49		0.75	0.019		0.030	
С	2.4		2.7	0.040		0.106	
c1	1.0		1.3	0.039		0.050	
D	15.4		16.0	0.606		0.629	
е		2.2			0.087		
e3	4.15		4.65	0.163		0.183	
F		3.8			0.150		
G	3		3.2	0.118		0.126	
Н			2.54			0.100	





57

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information or for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics. The ST logo is a trademark of STMicroelectronics

© 2000 STMicroelectronics - Printed in Italy - All Rights Reserved

STMicroelectronics GROUP OF COMPANIES Australia - Brazil - China - Finland - France - Germany - Hong Kong - India - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - U.S.A.

http://www.st.com

