


Main Features

| Symbol | Value | Unit |
|-------------------|------------|------|
| $I_{T(RMS)}$ | 1 | A |
| V_{DRM}/V_{RRM} | 600 to 800 | V |
| $I_{GT}(Q_i)$ | 3 to 25 | mA |

Description

The Z01 series is suitable for general purpose AC switching applications. They can be found in applications such as home appliances (electrovalve, pump, door lock, small lamp control), fan speed controllers,...

Different gate current sensitivities are available, allowing optimized performances when controlled directly from microcontrollers.



Order Codes

| Part Number | Marking |
|-------------|--|
| Z01xxA | See Ordering information on page 7 |
| Z01xxN | |

Table 1. Absolute maximum ratings

| Symbol | Parameter | Value | Unit | |
|--------------------|--|---|--------------------------------|------------|
| $I_{T(RMS)}$ | RMS on-state current (full sine wave) | SOT-223 $T_{tab} = 90^\circ C$ | 1 | A |
| | | TO-92 $T_L = 50^\circ C$ | | |
| I_{TSM} | Non repetitive surge peak on-state current (full cycle, T_j initial = $25^\circ C$) | F = 50 Hz t = 20 ms | 8 | A |
| | | F = 60 Hz t = 16.7 ms | 8.5 | |
| I^2t | I^2t Value for fusing | $t_p = 10$ ms | 0.35 | A^2s |
| di/dt | Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$, $t_r \leq 100$ ns | F = 120 Hz $T_j = 125^\circ C$ | 20 | A/ μs |
| I_{GM} | Peak gate current | $t_p = 20$ μs $T_j = 125^\circ C$ | 1 | A |
| $P_{G(AV)}$ | Average gate power dissipation | $T_j = 125^\circ C$ | 1 | W |
| T_{stg} T_j | Storage junction temperature range Operating junction temperature range | | - 40 to + 150 - 40 to + 125 | $^\circ C$ |

1 Characteristics

Table 2. Electrical characteristics ($T_j = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Test Conditions | Quadrant | | Z01 | | | | Unit |
|-------------------|--|--------------|-----|-----|----|----|-----|------------------|
| | | | | 03 | 07 | 09 | 10 | |
| $I_{GT}^{(1)}$ | $V_D = 12\text{ V}$ $R_L = 30\ \Omega$ | I - II - III | MAX | 3 | 5 | 10 | 25 | mA |
| | | IV | | 5 | 7 | 10 | 25 | |
| V_{GT} | | ALL | MAX | 1.3 | | | | V |
| V_{GD} | $V_D = V_{DRM}$ $R_L = 3.3\ \text{k}\Omega$ $T_j = 125^\circ\text{C}$ | ALL | MIN | 0.2 | | | | V |
| $I_H^{(2)}$ | $I_T = 50\ \text{mA}$ | | MX. | 7 | 10 | 10 | 25 | mA |
| I_L | $I_G = 1.2 I_{GT}$ | I - III - IV | MAX | 7 | 10 | 15 | 25 | mA |
| | | II | | 15 | 20 | 25 | 50 | |
| $dV/dt^{(2)}$ | $V_D = 67\% V_{DRM}$ gate open $T_j = 110^\circ\text{C}$ | | MIN | 10 | 20 | 50 | 100 | V/ μs |
| $(dV/dt)_c^{(2)}$ | $(dV/dt)_c = 0.44\ \text{A/ms}$ $T_j = 110^\circ\text{C}$ | | MIN | 0.5 | 1 | 2 | 5 | V/ μs |

1. minimum I_{GT} is guaranteed at 5% of I_{GT} max.

2. for both polarities of A2 referenced to A1.

Table 3. Static characteristics

| Symbol | Test Conditions | | | Value | Unit | |
|------------------------|--------------------------|--------------------------|---------------------------|-------|------|------------------|
| $V_{TM}^{(1)}$ | $I_{TM} = 1.4\ \text{A}$ | $t_p = 380\ \mu\text{s}$ | $T_j = 25^\circ\text{C}$ | MAX. | 1.56 | V |
| $V_{to}^{(1)}$ | Threshold voltage | | $T_j = 125^\circ\text{C}$ | MAX. | 0.95 | V |
| $R_d^{(1)}$ | Dynamic resistance | | $T_j = 125^\circ\text{C}$ | MAX. | 400 | $\text{m}\Omega$ |
| I_{DRM} I_{RRM} | $V_{DRM} = V_{RRM}$ | | $T_j = 25^\circ\text{C}$ | MAX. | 5 | μA |
| | | | $T_j = 125^\circ\text{C}$ | | 0.5 | mA |

1. for both polarities of A2 referenced to A1.

Table 4. Thermal resistances

| Symbol | Parameter | | Value | Unit |
|---------------|-----------------------|------------------------------------|-------|--------------------|
| $R_{th(j-t)}$ | Junction to tab (AC) | SOT-223 | 25 | $^\circ\text{C/W}$ |
| $R_{th(j-l)}$ | Junction to lead (AC) | TO-92 | 60 | |
| $R_{th(j-a)}$ | Junction to ambient | $S^{(1)} = 5\ \text{cm}^2$ SOT-223 | 60 | $^\circ\text{C/W}$ |
| | | TO-92 | 150 | |

1. S = Copper surface under tab.

Figure 1. Maximum power dissipation versus RMS on-state current (full cycle)




Figure 2. RMS on-state current versus ambient temperature (full cycle)




Figure 3. RMS on-state current versus ambient temperature (full cycle)




Figure 4. Relative variation of thermal impedance versus pulse duration




Figure 5. Relative variation of gate trigger current, holding current and latching current versus junction temperature (typical values)




Figure 6. Surge peak on-state current versus number of cycles




Figure 7. Non-repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 10$ ms and corresponding value of I^2t




Figure 8. On-state characteristics (maximum values)




Figure 9. Relative variation of critical rate of decrease of main current versus $(dV/dt)_c$ (typical values)




Figure 10. Relative variation of critical rate of decrease of main current versus junction temperature





Figure 11. SOT-223 Thermal resistance junction to ambient versus copper surface under tab (printed circuit board FR4, copper thickness: 35 μ m)



2 Ordering information scheme




Table 5. Product Selector

| Part Number | Voltage | | | Sensitivity | Type | Package |
|-------------|---------|-------|-------|-------------|----------|---------|
| | 600 V | 700 V | 800 V | | | |
| Z0103MA | X | | | 3 mA | Standard | TO-92 |
| Z0103MN | X | | | 3 mA | Standard | SOT-223 |
| Z0103SA | | X | | 3 mA | Standard | TO-92 |
| Z0103SN | | X | | 3 mA | Standard | SOT-223 |
| Z0103NA | | | X | 3 mA | Standard | TO-92 |
| Z0103NN | | | X | 3 mA | Standard | SOT-223 |
| Z0107MA | X | | | 5 mA | Standard | TO-92 |
| Z0107MN | X | | | 5 mA | Standard | SOT-223 |
| Z0107SA | | X | | 5 mA | Standard | TO-92 |
| Z0107SN | | X | | 5 mA | Standard | SOT-223 |
| Z0107NA | | | X | 5 mA | Standard | TO-92 |
| Z0107NN | | | X | 5 mA | Standard | SOT-223 |
| Z0109MA | X | | | 10 mA | Standard | TO-92 |
| Z0109MN | X | | | 10 mA | Standard | SOT-223 |
| Z0109SA | | X | | 10 mA | Standard | TO-92 |
| Z0109SN | | X | | 10 mA | Standard | SOT-223 |
| Z0109NA | | | X | 10 mA | Standard | TO-92 |
| Z0109NN | | | X | 10 mA | Standard | SOT-223 |
| Z0110MA | X | | | 25 mA | Standard | TO-92 |
| Z0110MN | X | | | 25 mA | Standard | SOT-223 |
| Z0110SA | | X | | 25 mA | Standard | TO-92 |
| Z0110SN | | X | | 25 mA | Standard | SOT-223 |
| Z0110NA | | | X | 25 mA | Standard | TO-92 |
| Z0110NN | | | X | 25 mA | Standard | SOT-223 |

3 Packaging information

Table 6. SOT-223 Dimensions

| REF. | Dimensions | | | | | |
|------|-------------|------|------|--------|-------|-------|
| | Millimeters | | | Inches | | |
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A | | | 1.80 | | | 0.071 |
| A1 | | 0.02 | | | 0.001 | |
| B | 0.60 | 0.70 | 0.80 | 0.024 | 0.027 | 0.031 |
| B1 | 2.90 | 3.00 | 3.10 | 0.114 | 0.118 | 0.122 |
| c | 0.24 | 0.26 | 0.32 | 0.009 | 0.010 | 0.013 |
| D | 6.30 | 6.50 | 6.70 | 0.248 | 0.256 | 0.264 |
| e | | 2.3 | | | 0.090 | |
| e1 | | 4.6 | | | 0.181 | |
| E | 3.30 | 3.50 | 3.70 | 0.130 | 0.138 | 0.146 |
| H | 6.70 | 7.00 | 7.30 | 0.264 | 0.276 | 0.287 |
| V | 10° max | | | | | |

Figure 12. SOT-223 Footprint dimensions (in millimeters)




Table 7. TO-92 Dimensions

| REF. | DIMENSIONS | | | | | |
|------|-------------|------|------|--------|-------|-------|
| | Millimeters | | | Inches | | |
| | Min. | Typ. | Max. | Min. | Typ. | Max. |
| A | | 1.35 | | | 0.053 | |
| B | | | 4.70 | | | 0.185 |
| C | | 2.54 | | | 0.100 | |
| D | 4.40 | | | 0.173 | | |
| E | 12.70 | | | 0.500 | | |
| F | | | 3.70 | | | 0.146 |
| a | | | 0.50 | | | 0.019 |

4 Ordering information

| Ordering type ⁽¹⁾ | Marking ⁽¹⁾ | Package | Weight | Base quantity | Delivery mode |
|------------------------------|------------------------|---------|--------|---------------|---------------|
| Z01xyA 1AA2 | Z01xyA | TO-92 | 0.2 g | 2500 | Bulk |
| Z01xyA 2AL2 | Z01xyA | TO-92 | 0.2 g | 2000 | Ammopack |
| Z01xyA 5AL2 | Z01xyA | TO-92 | 0.2 g | 2000 | Tape and reel |
| Z0103yN 5AA4 | Z3y | SOT-223 | 0.12 g | 1000 | Tape and reel |
| Z0107yN 5AA4 | Z7y | SOT-223 | 0.12 g | 1000 | Tape and reel |
| Z0109yN 5AA4 | Z9y | SOT-223 | 0.12 g | 1000 | Tape and reel |

1. xx = sensitivity, y = voltage

5 Revision History

| Date | Revision | Description of Changes |
|-------------|----------|---|
| Oct-2001 | 4 | Last update. |
| 10-Feb-2005 | 5 | Package: TO-92 tape and reel delivery mode 5AL2 added. |
| 09-May-2005 | 6 | Table 4 on page 2: typo. mistake corrected 1. (dV/dt) _c instead of (dI/dt) _c 2. V/μs unit instead of A/ms |
| 21-Apr-2006 | 7 | Reformatted to current standard. Table 2 on page 2: Typo corrected. Values for I _{GT} split into two separate rows. |

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED REPRESENTATIVE OF ST, ST PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS, WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2006 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com