RoHS


COMPLIANT

GREEN (5-2008)\*\*



### Vishay Semiconductors

# Optocoupler, Phototransistor Output, High Reliability, 5000 V<sub>RMS</sub>, 110 °C Rated



### **DESCRIPTION**

The 110 °C rated SFH617A (DIP) feature a high current transfer ratio, low coupling capacitance and high isolation voltage. These couplers have a GaAs infrared diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a plastic DIP-4 package.

The coupling devices are designed for signal transmission between two electrically separated circuits.

The couplers are end-stackable with 2.54 mm spacing.

Creepage and clearance distances of > 8.0 mm are achieved with option 6. This version complies with IEC 60950 (DIN VDE 0805) for reinforced insulation up to an operation voltage of 400  $V_{RMS}$  or DC. Specifications subject to change.

### **FEATURES**

- Operating temperature from 55 °C to + 110 °C
- Good CTR linearity depending on forward current



- High collector emitter voltage, V<sub>CEO</sub> = 70 V
- · Low saturation voltage
- Fast switching times
- Low CTR degradation
- Temperature stable
- · Low coupling capacitance
- End stackable, 0.100" (2.54 mm) spacing
- High common mode interference immunity
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC

### Note

\* Please see document "Vishay Material Category Policy": www.vishay.com/doc?99902

### **APPLICATIONS**

- AC adapter
- SMPS
- PLC
- Factory automation
- · Game consoles

### **AGENCY APPROVALS**

- UL1577, file no. E52744
- cUL tested to CSA 22.2 bulletin 5A
- DIN EN 60747-5-2 (VDE 0884)/DIN EN 60747-5-5 (pending) available with option 1
- BSI IEC 60950; IEC 60065
- FIMKO
- CQC (pending)

ORDERING INFORMATION								
S F H 6 1 7 A - # X 0 # # T  PART NUMBER CTR PACKAGE OPTION TAPE AND REEL  Option 7  Option 9  8 mm typ.								
AGENCY CERTIFIED/PACKAGE		CTR	ł (%)					
UL, VDE, BSI, FIMKO, cUL	40 to 80	63 to 125	100 to 200	160 to 320				
DIP-4	SFH617A-1	SFH617A-2	SFH617A-3	SFH617A-4				
DIP-4, 400 mil, option 6	SFH617A-1X006	SFH617A-2X006	SFH617A-3X006	SFH617A-4X006				
SMD-4, option 7	SFH617A-1X007T	=	SFH617A-3X007T	-				
SMD-4, option 9	=	SFH617A-2X009T	=	-				
VDE, UL, BSI, FIMKO, cUL	40 to 80	63 to 125	100 to 200	160 to 320				
DIP-4	SFH617A-1X001	SFH617A-2X001	SFH617A-3X001	SFH617A-4X001				
DIP-4, 400 mil, option 6	SFH617A-1X016	SFH617A-2X016	SFH617A-3X016	SFH617A-4X016				
SMD-4, option 7	-	SFH617A-2X017T	SFH617A-3X017T (1)	-				
SMD-4, option 9	-	SFH617A-2X019T (1)	-	-				

### Notes

Rev. 2.1, 01-Feb-12

• Additional options may be possible, please contact sales office.

(1) Also available in tubes; do not add T to end.



ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	PARAMETER TEST CONDITION SYMBOL VALUE							
INPUT			·					
Reverse voltage		V <sub>R</sub>	6	V				
Forward current		I <sub>F</sub>	60	mA				
Forward surge current	t <sub>p</sub> ≤ 10 μs	I <sub>FSM</sub>	2.5	Α				
LED power dissipation	at 25 °C	P <sub>diss</sub>	70	mW				
OUTPUT			·					
Collector emitter voltage		V <sub>CEO</sub>	70	V				
Emitter collector voltage		V <sub>ECO</sub>	7	V				
Collector current		I <sub>C</sub>	50	mA				
Collector peak current	$t_p/T = 0.5, t_p \le 10 \text{ ms}$	I <sub>CM</sub>	100	mA				
Ouput power dissipation	at 25 °C	P <sub>diss</sub>	150	mW				
COUPLER			·					
Isolation test voltage (RMS)	t = 1 s	V <sub>ISO</sub>	5000	V <sub>RMS</sub>				
Isolation resistance	$V_{IO} = 500 \text{ V}, T_{amb} = 25 ^{\circ}\text{C}$	R <sub>IO</sub>	≥ 10 <sup>12</sup>	Ω				
isolation resistance	V <sub>IO</sub> = 500 V, T <sub>amb</sub> = 100 °C	R <sub>IO</sub>	≥ 10 <sup>11</sup>	Ω				
Operation temperature		T <sub>amb</sub>	- 55 to + 110	°C				
Storage temperature range		T <sub>stg</sub>	- 55 to + 150	°C				
Soldering temperature (1)	2 mm from case, ≤ 10 s	T <sub>sld</sub>	260	°C				

#### **Notes**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
  implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
  maximum ratings for extended periods of the time can adversely affect reliability.
- (1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)									
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT		
INPUT									
Forward voltage	$I_F = 60 \text{ mA}$		$V_{F}$		1.35	1.65	V		
Reverse current	V <sub>R</sub> = 6 V		I <sub>R</sub>		0.01	10	μA		
Capacitance	$V_R = 0 V$ , $f = 1 MHz$		Co		13		pF		
OUTPUT									
Collector emitter capacitance	$V_{CE} = 5 \text{ V}, f = 1 \text{ MHz}$		C <sub>CE</sub>		5.2		pF		
		SFH617A-1	I <sub>CEO</sub>		2	50	nA		
Collector emitter leakage aurrent	V <sub>CF</sub> = 10 V	SFH617A-2	I <sub>CEO</sub>		2 50	50	nA		
Collector emitter leakage current	v <sub>CE</sub> = 10 v	SFH617A-3	I <sub>CEO</sub>		5	100	nA		
		SFH617A-4	I <sub>CEO</sub>		5	100	nA		
COUPLER									
Collector emitter saturation voltage	I <sub>F</sub> = 10 mA, f = 1 MHz		V <sub>CEsat</sub>		0.25	0.4	V		
Coupling capacitance			C <sub>C</sub>		0.4		pF		

#### Note

 Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.




<b>CURRENT TRANSFER RATIO</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
		SFH617A-1	CTR	40		80	%
	$I_{\rm F} = 10$ mA, $V_{\rm CF} = 5$ V	SFH617A-2	CTR	63		125	%
	I <sub>F</sub> = 10 IIIA, V <sub>CE</sub> = 5 V	SFH617A-3	CTR	100		200	%
1-/1-		SFH617A-4	CTR	160		320	%
l <sub>C</sub> /l <sub>F</sub>	I <sub>F</sub> = 1 mA, V <sub>CE</sub> = 5 V	SFH617A-1	CTR	13	30		%
		SFH617A-2	CTR	22	45		%
		SFH617A-3	CTR	34	70		%
		SFH617A-4	CTR	56	90		%

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
NON-SATURATED		1	_				
Turn-on time	$I_F = 10 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 75 \Omega$		t <sub>on</sub>		3		μs
Rise time	$I_F = 10 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 75 \Omega$		t <sub>r</sub>		2		μs
Turn-off time	$I_F = 10 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 75 \Omega$		t <sub>off</sub>		2.3		μs
Fall time	$I_F = 10 \text{ mA}, V_{CC} = 5 \text{ V}, R_L = 75 \Omega$		t <sub>f</sub>		2		μs
Cut-off frequency	$I_F = 10 \text{ mA}, V_{CC} = 5 \text{ V}$		f <sub>CO</sub>		100		kHz
SATURATED					•		
	I <sub>F</sub> = 20 mA	SFH617A-1	t <sub>on</sub>		3		μs
Town and the co	I <sub>F</sub> = 10 mA	SFH617A-2	t <sub>on</sub>		4.2		μs
Turn-on time		SFH617A-3	t <sub>on</sub>		4.2		μs
	I <sub>F</sub> = 5 mA	SFH617A-4	t <sub>on</sub>		6		μs
	I <sub>F</sub> = 20 mA	SFH617A-1	t <sub>r</sub>		2		μs
Diag times	I <sub>F</sub> = 10 mA	SFH617A-2	t <sub>r</sub>		3		μs
Rise time		SFH617A-3	t <sub>r</sub>		3		μs
	I <sub>F</sub> = 5 mA	SFH617A-4	t <sub>r</sub>		4.6		μs
	I <sub>F</sub> = 20 mA	SFH617A-1	t <sub>off</sub>		18		μs
T # 1:		SFH617A-2	t <sub>off</sub>		23		μs
Turn-off time	I <sub>F</sub> = 10 mA	SFH617A-3	t <sub>off</sub>		23		μs
	I <sub>F</sub> = 5 mA	SFH617A-4	t <sub>off</sub>		25		μs
E ###	I <sub>F</sub> = 20 mA	SFH617A-1	t <sub>f</sub>		11		μs
	1 10 mA	SFH617A-2	t <sub>f</sub>		14		μs
Fall time	I <sub>F</sub> = 10 mA	SFH617A-3	t <sub>f</sub>		14		μs
	I <sub>F</sub> = 5 mA	SFH617A-4	t <sub>f</sub>		15		μs



### www.vishay.com

# Vishay Semiconductors



95 10804-3

Fig. 1 - Test Circuit, Non-Saturated Operation





Fig. 2 - Test Circuit, Saturated Operation



SAFETY AND INSULATION RATINGS								
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT		
Climatic classification (according to IEC 68 part 1)				55/110/21				
Comparative tracking index		CTI	175		399			
Rated impulse voltage		V <sub>IOTM</sub>			8	kV		
Maximum working voltages	Recurring peak voltage	V <sub>IORM</sub>			890	V		
Forward current		I <sub>SI</sub>			275	mA		
Power dissipation		P <sub>SO</sub>			400	mW		
Safety temperature		T <sub>SI</sub>			175	°C		
Creepage distance			7.0			mm		
Clearance distance			7.0			mm		
Isolation distance	per IEC 60950 2.10.5.1		0.4			mm		

### Note

According to DIN EN 60747-5-2 (VDE 0884). These optocouplers are suitable for "safe electrical insulation" only within the safety ratings.
 Compliance with the safety ratings shall be ensured by means of protective circuits.



### TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 4 - Forward Voltage vs. Forward Current




Fig. 5 - Collector Current vs. Collector Emitter Voltage (NS)




Fig. 6 - Collector Current vs. Collector Emitter Voltage (sat)




Fig. 7 - Leakage Current vs. Ambient Temperature




Fig. 8 - Normalized CTR (NS) vs. Ambient Temperature





Fig. 9 - Normalized CTR (sat) vs. Ambient Temperature








Fig. 10 - Normalized CTR (NS) vs. Forward Current




Fig. 11 - Normalized CTR (sat) vs. Forward Current




Fig. 12 - CTR Frequency vs. Phase Angle




Fig. 13 - CTR Frequency vs. Collector Current







Fig. 14 - Switching Time vs. Load Resistance





### **PACKAGE DIMENISONS** in millimeters

















# 20802-28 PACKAGE MARKING



### **Notes**

- VDE logo is only marked on option 1 parts. Option information is not marked on the part.
- Tape and reel suffix (T) is not part of the package marking.



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.