

## Features

- Efficiency up to 97%,Non isolated, no need for heatsinks
- Pin-out compatible with LM78XX Linears
- Very low profile( L\*W\*H=11.5\*7.5\*10.2 )
- Wide input range.(4.75V ~ 34V)
- Short circuit protection, Thermal shutdown
- Non standard outputs available as specials between 1.5V ~15.5V
- Low ripple and noise

**INNOLINE**  
DC/DC-Converter

# R-78xx-0.5 Series

**0.5 AMP**  
**SIP3**  
**Single Output**

### Selection Guide

| Part Number | Input Range (1) | Output Voltage | Output Current | Efficiency |          |
|-------------|-----------------|----------------|----------------|------------|----------|
|             |                 |                |                | Min. Vin   | Max. Vin |
| SIP3        | (V)             | (V)            | (A)            | (%)        | (%)      |
| R-781.5-0.5 | 4.75 – 30       | 1.5            | 0.5            | 73         | 63       |
| R-781.8-0.5 | 4.75 – 34       | 1.8            | 0.5            | 82         | 71       |
| R-782.5-0.5 | 4.75 – 34       | 2.5            | 0.5            | 87         | 77       |
| R-783.3-0.5 | 4.75 – 34       | 3.3            | 0.5            | 91         | 81       |
| R-785.0-0.5 | 6.5 – 34        | 5.0            | 0.5            | 94         | 86       |
| R-786.5-0.5 | 8.0 – 34        | 6.5            | 0.5            | 95         | 88       |
| R-789.0-0.5 | 11 – 34         | 9.0            | 0.5            | 96         | 92       |
| R-7812-0.5  | 15 – 34         | 12             | 0.5            | 97         | 94       |
| R-7815-0.5  | 18 – 34         | 15             | 0.5            | 97         | 95       |

Note 1:1.5V Output can be unstable with Vin>30VDC


### Description

The R-78xx-Series high efficiency switching regulators are ideally suited to replace 78xx linear regulators and are pin compatible. The efficiency of up to 97% means that very little energy is wasted as heat so there is no need for any heat sinks with their additional space and mounting costs. Low ripple and noise figures and a short circuit input current of typically only 7mA round off the specifications of this versatile converter series.

This R-78xx-0.5 is fully certified to EN 60601-1-2 (Medical Equipment), EN 55022 (Emissions), and EN55024 (Immunity) EMC Standards.




## Derating-Graph (Ambient Temperature)



Specifications (refer to the standard application circuit, Ta: 25°C)

| Characteristics                                           | Conditions                                                   | Min.                | Typ.                           | Max.              |
|-----------------------------------------------------------|--------------------------------------------------------------|---------------------|--------------------------------|-------------------|
| Input Voltage Range                                       | 1.5V                                                         | 4.75                |                                | 30.0V             |
|                                                           | 1.8V to 15.5V                                                | 4.75                |                                | 34.0V             |
| Output Voltage Range (for customized parts)               | All Series                                                   | 1.25                |                                | 15.5V             |
| Output Current                                            | All Series                                                   | 50                  |                                | 500mA             |
| Output Current Limit                                      | All Series                                                   |                     |                                | 2000mA            |
| Short Circuit Input Current                               | All Series                                                   |                     | 10                             | 30mA              |
| Internal Power Dissipation                                |                                                              |                     |                                | 0.4W              |
| Short Circuit Protection                                  |                                                              |                     | Continuous, automatic recovery |                   |
| Output Voltage Accuracy (At 100% Load)                    | All Series                                                   |                     | ±2                             | ±3%               |
| Line Voltage Regulation (Vin = min. to max. at full load) | 1.5V to 6.5V                                                 |                     | 0.2                            | 0.4%              |
|                                                           | 9V to 15.5V                                                  |                     | 0.1                            | 0.2%              |
| Load Regulation (10 to 100% full load)                    | 1.5V to 6.5V                                                 |                     | 0.4                            | 0.6%              |
|                                                           | 9V to 15.5V                                                  |                     | 0.25                           | 0.4%              |
| Dynamic Load Stability                                    | 100% <-> 50% load                                            |                     | ±75mV                          |                   |
|                                                           | 100% <-> 10% load                                            |                     |                                | ±100mV            |
| Ripple & Noise (without Output Capacitor)                 | 1.5V to 6.5V                                                 |                     | 20mVp-p                        | 30mVp-p           |
|                                                           | 9V to 15.5V                                                  |                     | 30mVp-p                        | 40mVp-p           |
| Ripple & Noise (with Output Capacitor=100µF)              | 1.5V to 6.5V                                                 |                     | 15mVp-p                        | 20mVp-p           |
|                                                           | 9V to 15.5V                                                  |                     | 25mVp-p                        | 35mVp-p           |
| Temperature Coefficient                                   | -40°C ~ +85°C ambient                                        |                     |                                | 0.015%/°C         |
| Max capacitance Load                                      |                                                              |                     |                                | 220µF             |
| Switching Frequency                                       |                                                              | 280                 | 330                            | 380kHz            |
| Quiescent Current                                         | Vin = min. to max. at 0% load                                |                     | 5                              | 7mA               |
| Operating Temperature Range                               |                                                              | -40°C               |                                | +85°C             |
| Operating Case Temperature                                |                                                              |                     |                                | +100°C            |
| Storage Temperature Range                                 |                                                              | -55°C               |                                | +125°C            |
| Case Thermal Impedance                                    |                                                              |                     |                                | 70°C / W          |
| Thermal Shutdown                                          | Internal IC junction                                         |                     | +160°C                         |                   |
| MTBF (+25°C)                                              | Detailed Information see<br>Application Notes chapter "MTBF" | using MIL-HDBK 217F |                                | 21098 x 10³ hours |
| (+71°C)                                                   |                                                              | using MIL-HDBK 217F |                                | 4212 x 10³ hours  |

Standard Application Circuit









To protect the converter during power-up, use soft start Vin and C1=47µF

Characteristics


Efficiency

Ripple




Application Examples

High efficiency, isolated, dual unregulated outputs







Isolated (up to 6KV), wide Input range regulated output




Package Style and Pinning (mm)

SIP3 PIN Package



Recommended Footprint Details



Pin Connections

| Pin # |       |
|-------|-------|
| 1     | +Vin  |
| 2     | GND   |
| 3     | +Vout |

xx.x ±0.5mm  
xx.xx ±0.25mm