


New Jersey Semi-Conductor Products, Inc.

20 STERN AVE.
SPRINGFIELD, NEW JERSEY 07081
U.S.A.

N-Channel Junction Field-Effect Transistors

BF 245 A
BF 245 B
BF 245 C

BF 245 A, B, and C are N-channel junction field-effect transistors in plastic package similar to TO 92 (10 A 3 DIN 41868). They are particularly suitable for use in dc, AF and RF amplifiers.



Maximum ratings

Drain-source voltage	$\pm V_{DS}$	30	V
Drain-gate voltage ($I_S = 0$)	$+V_{DG}$	30	V
Gate-source voltage ($I_D = 0$)	$-V_{GS}$	30	V
Drain current	I_D	25	mA
Gate current	I_G	10	mA
Junction temperature	T_J	150	°C
Storage temperature range	T_{STG}	-65 to +150	°C
Total power dissipation ($T_{amb} \leq 75^\circ\text{C}$) ¹⁾	P_{tot}	300	mW

Thermal resistance

Junction to ambient air	R_{thJA}	≤ 250	K/W ¹⁾
-------------------------	------------	-------	-------------------

Static characteristics ($T_J = 25^\circ\text{C}$)

Gate cutoff current ($-V_{GS} = 20\text{ V}, V_{DS} = 0$)	$-I_{GS}$	≤ 5	nA
($-V_{GS} = 20\text{ V}, V_{DS} = 0, T_J = 125^\circ\text{C}$)	$-I_{GS}$	≤ 500	nA
Gate-source breakdown voltage ($-I_G = 1\text{ }\mu\text{A}, V_{DS} = 0$)	$-V_{BRIGSS}$	≥ 30	V
Drain-source short-circuit current ($V_{DS} = 15\text{ V}, V_{GS} = 0$)	BF 245 A: I_{DSS} BF 245 B: I_{DSS} BF 245 C: I_{DSS}	2.0 to 8.5 8 to 15 12 to 25	mA ²⁾
Gate-source voltage ($V_{DS} = 15\text{ V}, I_D = 200\text{ }\mu\text{A}$)	BF 245 A: $-V_{GS}$ BF 245 B: $-V_{GS}$ BF 245 C: $-V_{GS}$	0.4 to 2.2 1.8 to 3.8 3.2 to 7.5	V ²⁾
Gate-source pinch-off voltage ($V_{DS} = 15\text{ V}, I_D = 10\text{ nA}$)	$-V_P$	0.5 to 8.0	V

Dynamic characteristics ($T_{amb} = 25^\circ\text{C}$)

Four-pole characteristics ($V_{DS} = 15\text{ V}, V_{GS} = 0, f = 1\text{ kHz}$)	$ y_{21s} $ $ y_{22s} $	3.0 to 6.5 25	mS μS
($V_{DS} = 15\text{ V}, V_{GS} = 0, f = 200\text{ MHz}$)	g_{11} $ y_{21s} $	250 8	μS mS
($V_{DS} = 20\text{ V}, -V_{GS} = 1\text{ V}, f = 1\text{ MHz}$)	g_{22s} C_{11s} C_{12s} C_{22s}	40 4.0 1.1 1.6	μS pF pF pF
Cutoff frequency of short-circuit forward transfer admittance ¹⁾ ($V_{DS} = 15\text{ V}, V_{GS} = 0$)	f_{y21s}	700	MHz
Noise figure ($V_{DS} = 15\text{ V}, V_{GS} = 0, R_g = 1\text{ k}\Omega$, $f = 100\text{ MHz}, T_{amb} = 25^\circ\text{C}$)	NF	1.6	dB

