

## Technical Data Sheet

# 3 mm Small Flange with Stand-off LED,T-1

**264-7SUGC/S400-A4**

### Features

- High luminous power.
- Can be driven at low current
- 2.54mm lead spacing
- Available on tape and reel.

### Descriptions

- The series is specially designed for applications requiring higher brightness.
- The LED lamps are available with different colors,intensities,epoxy colors,etc.



### Applications

- TV set.
- Monitor.
- Telephone.
- Computer.


### Device Selection Guide

Chip		Lens Color
Material	Emitted Color	
InGaN	Super Green	Water Clear

**B90052012,9009046**

**264-7SUGC/S400-A4**

**Package Dimensions**



**Notes:**

- All dimensions are in millimeters, tolerance is 0.25mm except being specified.
- Lead spacing is measured where the lead emerges from the package.
- Protruded resin under flange is 1.5mm Max LED.

**Absolute Maximum Ratings (Ta=25°C)**

Parameter	Symbol	Rating	Units
Forward Current	I <sub>F</sub>	25	mA
Pulse Forward Current <sup>*1</sup>	I <sub>FP</sub>	100	mA
Operating Temperature	T <sub>opr</sub>	-40 ~ +85	°C
Storage Temperature	T <sub>stg</sub>	-40 ~ +100	°C
Electrostatic Discharge	ESD	150	V
Soldering Temperature <sup>*2</sup>	T <sub>sol</sub>	260 ± 5	°C
Power Dissipation	P <sub>d</sub>	120	mW
Reverse Voltage	V <sub>R</sub>	5	V

**Notes:** \*1:I<sub>FP</sub> Conditions--Pulse Width ≤ 10msec and Duty ≤ 1/10.

\*2:Soldering time ≤ 5 seconds.

**Electro-Optical Characteristics (Ta=25°C)**

Parameter	Symbol	Condition	Min.	Typ.	Max.	Units
Forward Voltage	$V_F$	$I_F=20mA$	3.2	3.5	4.3	V
Reverse Current	$I_R$	$V_R=5V$	--	--	50	$\mu A$
Luminous Intensity	$I_V$	$I_F=20mA$	1600	2500	--	mcd
Viewing Angle	$2\theta 1/2$	$I_F=20mA$	--	25	--	deg
Peak Wavelength	$\lambda_p$	$I_F=20mA$	--	530	--	nm
Dominant Wavelength	$\lambda_d$	$I_F=20mA$	--	525	--	nm
Spectrum Radiation Bandwidth	$\Delta \lambda$	$I_F=20mA$	--	35	--	nm

**Typical Electro-Optical Characteristics Curves**

