



MBR2545CT
MBRB2545CT
MBR2545CT-1

SCHOTTKY RECTIFIER

30 Amp


Major Ratings and Characteristics

Characteristics	Values	Units
$I_{F(AV)}$ Rectangular waveform (Per Device)	30	A
I_{FRM} @ $T_C = 130^\circ\text{C}$ (Per Leg)	30	A
V_{RRM}	35/45	V
I_{FSM} @ $tp = 5 \mu\text{s}$ sine	1060	A
V_F @ 30 Apk, $T_J = 125^\circ\text{C}$	0.73	V
T_J range	-65 to 150	$^\circ\text{C}$

Description/ Features

This center tap Schottky rectifier has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 150°C junction temperature. Typical applications are in switching power supplies, converters, free-wheeling diodes, and reverse battery protection.

- 150°C T_J operation
- Center tap TO-220 and D²Pak packages
- Low forward voltage drop
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



Voltage Ratings

Parameters	MBR2535CT MBRB2535CT MBR2535CT-1	MBR2545CT MBRB2545CT MBR2545CT-1
V_R Max. DC Reverse Voltage (V)	35	45
V_{RWM} Max. Working Peak Reverse Voltage (V)		

Absolute Maximum Ratings

Parameters	Values	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current (Per Leg) (Per Device)	15	A	@ $T_C = 130^\circ\text{C}$, (Rated V_R)
	30		
I_{FRM} Peak Repetitive Forward Current (Per Leg)	30	A	Rated V_R , square wave, 20kHz $T_C = 130^\circ\text{C}$
I_{FSM} Non Repetitive Peak Surge Current	1060	A	5 μs Sine or 3 μs Rect. pulse Following any rated load condition and with rated V_{RWM} applied Surge applied at rated load conditions halfwave, single phase, 60Hz
	150		
E_{AS} Non-Repetitive Avalanche Energy	16	mJ	(Per Leg) $T_J = 25^\circ\text{C}$, $I_{AS} = 2$ Amps, $L = 8$ mH
I_{AR} Repetitive Avalanche Current (Per Leg)	2	A	Current decaying linearly to zero in 1 μsec Frequency limited by T_J max. $V_A = 1.5 \times V_R$ typical

Electrical Specifications

Parameters	Values	Units	Conditions
V_{FM} Max. Forward Voltage Drop (1)	0.82	V	@ 30A $T_J = 25^\circ\text{C}$
	0.73	V	@ 30A $T_J = 125^\circ\text{C}$
I_{RM} Max. Instantaneous Reverse Current (1)	0.2	mA	$T_J = 25^\circ\text{C}$
	40	mA	$T_J = 125^\circ\text{C}$ Rated DC voltage
$V_{F(TO)}$ Threshold Voltage	0.355	V	$T_J = T_J$ max.
r_t Forward Slope Resistance	12.3	m Ω	
C_T Max. Junction Capacitance	700	pF	$V_R = 5V_{DC}$, (test signal range 100Khz to 1Mhz) 25°C
L_S Typical Series Inductance 8.0	nH		Measured from top of terminal to mounting plane
dv/dt Max. Voltage Rate of Change (Rated V_R)	10000	V/ μs	

(1) Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters	Values	Units	Conditions
T_J Max. Junction Temperature Range	-65 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-65 to 175	$^\circ\text{C}$	
R_{thJC} Max. Thermal Resistance Junction to Case (Per Leg)	1.5	$^\circ\text{C}/\text{W}$	DC operation
R_{thCS} Typical Thermal Resistance Case to Heatsink	0.50	$^\circ\text{C}/\text{W}$	Mounting surface, smooth and greased Only for TO-220
wt Approximate Weight	2 (0.07)	g (oz.)	
T Mounting Torque	Min. 6 (5)	Kg-cm (lbf-in)	Non-lubricated threads
	Max. 12 (10)		




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)

- (2) Formula used: $T_c = T_j - (Pd + Pd_{REV}) \times R_{thJC}$;
 Pd = Forward Power Loss = $I_{F(AV)} \times V_{FM}$ @ $(I_{F(AV)} / D)$ (see Fig. 6);
 Pd_{REV} = Inverse Power Loss = $V_{R1} \times I_R (1 - D)$; I_R @ V_{R1} = rated V_R

Ordering Information Table

Device Code					
MBR	B	25	45	CT	-1
①	②	③	④	⑤	⑥

- 1** - Essential Part Number
- 2** - B = Surface Mount
None = TO-220
- 3** - Current Rating
- 4** - Voltage code: Code = V_{RRM}

35	= 35V
45	= 45V
- 5** - CT= Essential Part Number
- 6** - -1 = TO-262
None = TO-220

Outline Table


The drawing shows the following dimensions:

- Top View:**
 - Overall width: 10.54 (0.41) MAX.
 - Terminal 1 width: 3.78 (0.15)
 - Terminal 2 width: 3.54 (0.14)
 - Terminal 3 width: 2.92 (0.11)
 - Terminal 2 to edge: 2.54 (0.10)
 - Terminal 1 to edge: 15.24 (0.60)
 - Terminal 2 to edge: 14.84 (0.58)
 - Terminal 3 to edge: 14.09 (0.55)
 - Terminal 1 to edge: 13.47 (0.53)
 - Terminal 1 to edge: 1.40 (0.05)
 - Terminal 1 to edge: 1.15 (0.04)
 - Terminal 1 to edge: 0.94 (0.04)
 - Terminal 1 to edge: 0.69 (0.03)
 - Terminal 2 to edge: 3.96 (0.16)
 - Terminal 2 to edge: 3.55 (0.14)
 - Terminal 2 to edge: 2.04 (0.080) MAX.
- Side View:**
 - Lead height: 6.48 (0.25)
 - Lead height: 6.23 (0.24)
 - Lead diameter: 1.32 (0.05)
 - Lead diameter: 1.22 (0.05)
 - Lead angle: 2°
 - Lead diameter: 0.10 (0.004)
 - Lead diameter: 2.89 (0.11)
 - Lead diameter: 2.64 (0.10)
- Detail View:**
 - Terminal width: 4.57 (0.18)
 - Terminal width: 4.32 (0.17)
 - Terminal width: 0.61 (0.02) MAX.
 - Terminal width: 5.08 (0.20) REF.


Conform to JEDEC outline TO-220AB
 Dimensions are in millimeters and (inches)

Pinout: 1: ANODE, 2: COMMON CATHODE, 3: ANODE


Outline Table



Tape & Reel Information



Outline Table



Data and specifications subject to change without notice.
 This product has been designed and qualified for Industrial Level.
 Qualification Standards can be found on IR's Web site.