
## **Kingbright**

## T-1 (3mm) SOLID STATE LAMP

L-934SGD SUPER BRIGHT GREEN Features Description •LOW POWER CONSUMPTION. The Super Bright Green source color devices are made •POPULAR T-1 DIAMETER PACKAGE. with Gallium Phosphide Green Light Emitting Diode. •GENERAL PURPOSE LEADS •RELIABLE AND RUGGED. •LONG LIFE - SOLID STATE RELIABILITY. •AVAILABLE ON TAPE AND REEL. •RoHS COMPLIANT.

#### **Package Dimensions**



3. Lead spacing is measured where the leads emerge from the package.

4. Specifications are subject to change without notice.

Notes:

**REV NO: V.5 CHECKED:** Allen Liu DATE: APR/07/2005 DRAWN: B.H.LI

## Kingbright

#### **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) @ 20mA		Viewing Angle
			Min.	Тур.	2 <del>0</del> 1/2
L-934SGD	SUPER BRIGHT GREEN (GaP)	GREEN DIFFUSED	18	40	60 <b>°</b>

Note:

1.  $\theta$ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

### Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Green	565		nm	IF=20mA
λD	Dominant Wavelength	Super Bright Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Green	30		nm	IF=20mA
С	Capacitance	Super Bright Green	15		pF	VF=0V;f=1MHz
Vf	Forward Voltage	Super Bright Green	2.2	2.5	V	IF=20mA
IR	Reverse Current	Super Bright Green		10	uA	VR = 5V

### Absolute Maximum Ratings at TA=25°C

Parameter	Super Bright Green	Units			
Power dissipation	105	mW			
DC Forward Current	25	mA			
Peak Forward Current [1]	140	mA			
Reverse Voltage	5	V			
Operating/Storage Temperature	-40°C To +85°C				
Lead Solder Temperature [2]	260°C For 3 Seconds				
Lead Solder Temperature [3]	260°C For 5 Seconds	260°C For 5 Seconds			


Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.

3. 5mm below package base.

# Kingbright



REV NO: V.5 CHECKED: Allen Liu DATE: APR/07/2005 DRAWN: B.H.LI