Features

Regulated Converters

Constant Current Output

Power LED Driver

Wide Input Voltage Range

PWM/Digital Dimming and Analogue Voltage Dimming

Short Circuit Protected

96% Efficiency

Description

Rev.2

The RCD series is a step-down constant current source designed for driving high power white LEDs. Standard output currents available are 300mA, 350mA, 500mA, 600mA and 700mA to make this driver compatible with a wide range of LEDs from many different manufacturers without the need for any external components. Despite its compact size, the RCD series is fully featured with very high efficiency, wide input voltage range, high ambient operating temperature and two means of LED dimming: PWM/digital control and analogue voltage dimming. Both dimming controls are independent and can be combined. The driver is also designed to be as reliable as the LEDs it is driving, even at the full operating temperature of 85°C. A wired version is also available.

Selection Guide Part Input Output **Output** Dimming Mounting Number Range Current Voltage Control Style (mA) (VDC) (V) RCD-24-0.30 Digital + Analogue 4.5-36V 0-300 2-32 **PCB** RCD-24-0.35 4.5-36V 0-350 2-32 Digital + Analogue **PCB** RCD-24-0.50 4.5-36V 0-500 2-32 Digital + Analogue **PCB** RCD-24-0.60 4.5-36V 0-600 2-32 Digital + Analogue **PCB** RCD-24-0.70 4.5-36V 0-700 2-32 Digital + Analogue **PCB** RCD-24-0.30/W 4.5-36V 300 2-32 none Wired RCD-24-0.35/W 4.5-36V 350 2-32 Wired none RCD-24-0.50/W 4.5-36V 500 2-32 Wired none RCD-24-0.60/W 4.5-36V 600 2-32 none Wired RCD-24-0.70/W 4.5-36V 700 2-32 Wired none

Specifications

(typical at 25°C, nominal input voltage, rated output current unless otherwise specified)


Input Voltage (absolute maximum)	36VDC max.		
Recommended Input Voltage	5V min. / 24	5V min. / 24V typ. / 36VDC max.	
Input Filter		Capacitor	
Output Voltage Range	Vin=36V	2V min. / 32V max.	
Output Current Range	Vin - Vout >1.5~4V	300mA-700mA	
Output Current Accuracy	300mA-700mA	±2% typ.	
Internal Power Dissipation	Load of 5 LEDs	700mW	
Output Current Stability	Vin=36V, Vout =2~32V	±1% max	
Output Ripple and Noise (20MHz limited)	Vin=36V, Vout =2~32V	120mVp-p max	
Temperature Coefficient	-40~+85°C ambient	±0.015%/°C max.	
Maximum Capacitive Load		100μF	
Operating Frequency	210 kHz min/ 260k	210 kHz min/ 260kHz typ./ 300kHz max	
Efficiency at Full Load		97% max.	
Short Circuit Protection	Regulated a	Regulated at rated output current	
Operating Temperature Range	300mA/350mA	-40°C to +85°C	
(free air convection)	500mA	-40°C to +80°C	
	600mA	-40°C to +75°C	
	700mA	-40°C to +71°C	
Storage Temperature Range		-55°C to +125°C	
Maximum Case Temperature		100°C	
Thermal Impedance	Natural Convection	55°C/Watt	

INNOLINE

DC/DC-Converter

RCD-24 Series

Constant Current **Single Output**






Derating Graph

(Ambient Temperature)

RCD-24-0.35/0.70



continued on next page


INNOLINE DC/DC-Converter

RCD-24 Series


Specifications -Continued

Case Material		Non Co	nductive Black Plastic	
Potting Material			Epoxy (UL94-V0)	
Dimensions			22.1 x 12.6 x 8.5mm	
Weight			4.5g	
Wave Soldering Profile			Max. 265°C/10 sec.	
PWM Dimming and ON	PWM Dimming and ON/OFF Control (Leave open if not used)			
Remote ON/OFF		DC/DC ON	Open or OV <vr<0.6v< td=""></vr<0.6v<>	
		DC/DC OFF (Standby)	0.6 <vr<2.9v< td=""></vr<2.9v<>	
		DC/DC OFF (Shutdown)	2.9V <vr<6v< td=""></vr<6v<>	
Remote Pin Drive Curren	t	Vr=5V	1mA max.	
Quiescent Input Current in Shutdown Mode		Vin=36V, Vr>2.9V	200μA max.	
Maximum PWM Frequen	Maximum PWM Frequency for Linear Operation (measured 10%~90% Dimming) 200Hz			
Analogue Dimming Cor	ntrol (leave open if not used)			
Input Voltage Range			0 - 15V	
Control Voltage Range Li	mits	Full On	$0.13V \pm 50 \text{mV}$	
(see Graph)		Full Off	$4.5V \pm 50 \text{mV}$	
Analogue Pin Drive Curre	ent	Vc=5V	0.2mA max.	
Environmental				
Relative Humidity		5% to 95%	RH, non-condensing	
Conducted Emissions	(all series, see note)	EN55022	Class B	
Radiated Emissions	(all series except 700mA)	EN55022	Class B	
ESD	(all series)	EN61000-4-2	Class A	
Radiated Immunity	(all series)	EN61000-4-3	Class A	
Fast Transient	(all series)	EN61000-4-4	Class A	
Conducted Immunity	(all series)	EN61000-4-6	Class A	
MTBF (RCD-24-0.70, Nominal Vin, Full Load)		+25°C	605 x 10 ³ hours	
using MIL-HDBK 217F		+71°C	516 x 10 ³ hours	

Vin = 24V, lout = 300-700mA




Vin = 32V, lout = 300-700mA



Note: Requires an input filter to meet EN55022 ClassB conducted emissions, see below.


Class B Filter Suggestion







RCD-24 Series

Analogue Dimming Control and Application Circuit Examples







LED DIMMER for up to 7 white LEDs



Digital Dimming Control



* Max output current can also be set using Analogue input




INNOLINE DC/DC-Converter


RCD-24 Series

Package Style and Pinning

PCB Mounting Style













Wired Style





Recommended Footprint Details





Pin Conn	ections RCD-	-24 Series
Pin #	Out	Comments
1	+Vin	DC Supply
2	Analogue Dimming	Leave open if not used
3	PWM/ON/OFF	Leave open if not used
4	GND	Do not connect to -Vout
5	-Vout	LED Cathode Connection
6	+Vout	LED Anode Connection

XX.X \pm 0.5 mm XX.XX \pm 0.25 mm Pin Tolerance \pm 0.1 mm

Wire Connections		RCD-24/W Series	
Wire #	Out	Comments	
1 (Red)	+Vin	DC Supply	
4 (Black)	GND	Do not connect to -Vout	
5 (Brown)	-Vout	LED Cathode Connection	
6 (Yellow)	+Vout	LED Anode Connection	

Wire length = 100mm + 10mm stripped & tinned = 110mm total

Wire outside diameter = 1.6mm
Wire core diameter = 0.75mm


Wire core diameter = 0.75 mm

Wire is UL/CSA listed/ 22AWG / 300V Rated

Standard Application Circuits

+Vin ORD-24-xxx GND ORD-24-xxx Analogue Dim CRCD-24-xxx Last LED Last LED CRCD-24-xxx

MULTIPLE LED DRIVER (up to 20 LEDS)



Driving Two Strings of 350mA LEDs with one 700mA Driver.