

1.8mm SOLID STATE LAMP

L-2060ID

HIGH EFFICIENCY RED


Features

- •1.8mm DIAMETER SMALL SIZE LED LAMP.
- •ULTRA BRIGHTNESS IS AVAILABLE.
- •RELIABLE AND RUGGED.
- •VERSATILE MOUNTING ON P.C. BOARD OR PANEL.
- •AVAILABLE IN DIFFUSED LENS.
- •RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions



Notes:

- All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.

 3. Lead spacing is measured where the lead emerge from the package.

4. Specifications are subject to change without notice.

SPEC NO: DSAA5504 **REV NO: V.7** DATE: MAR/17/2005 PAGE: 1 OF 3 APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (m @ 10	,	Viewing Angle
		,.	Min.	Тур.	201/2
L-2060ID	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	8	15	70°

Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	IF=20mA
λD	Dominant Wavelength	High Efficiency Red	625		nm	Ir=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	IF=20mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
VF	Forward Voltage	High Efficiency Red	2.0	2.5	V	IF=20mA
IR	Reverse Current	High Efficiency Red		10	uA	VR = 12V

Absolute Maximum Ratings at TA=25°C

Parameter	High Efficiency Red	Units		
Power dissipation	105	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	160	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	ure [2] 260°C For 3 Seconds			
Lead Solder Temperature [3]	der Temperature [3] 260°C For 5 Seconds			

Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAA5504 **REV NO: V.7** DATE: MAR/17/2005 PAGE: 2 OF 3


APPROVED: J. Lu

CHECKED: Allen Liu

DRAWN: S.H.CHEN


 $^{1. \}theta 1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright





High Efficiency Red


L-2060ID











Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

- 1. Wavelength: +/-1nm
- 2. Luminous Intensity: +/-15%
- 3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAA5504 REV NO: V.7 DATE: MAR/17/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN