

5mm ROUND LED LAMP

PRELIMINARY SPEC

Part Number: L-9294SURCK

Hyper Red


Features

- High luminous white emission
- Low power consumption.
- General purpose leads.
- Reliable and rugged.
- Long life solid state reliability.
- RoHS compliant.

Description

The Hyper Red source color devices are made with Al-GaInP on GaAs substrate Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
- Lead spacing is measured where the leads emerge from the package.
 Specifications are subject to change without notice.





SPEC NO: DSAJ2818 **REV NO: V.1** DATE: APR/07/2009 PAGE: 1 OF 4 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Ting.Li ERP: 1101025550

Kingbright

Selection Guide

Part No.	Dice	lv (mcd) [2] Dice Lens Type @ 20mA		,	Viewing Angle [1]
			Min.	Тур.	201/2
L-9294SURCK	Hyper Red (AlGaInP)	WATER CLEAR	180	450	130°

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value. 2. Luminous intensity/ luminous Flux: +/-15%.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Hyper Red	650		nm	IF=20mA
λD [1]	Dominant Wavelength	Hyper Red	630		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Hyper Red	28		nm	IF=20mA
С	Capacitance	Hyper Red	35		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Hyper Red	1.95	2.5	V	IF=20mA
lr	Reverse Current	Hyper Red		10	uA	V _R = 5V

- Notes: 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.


Absolute Maximum Ratings at TA=25°C

Parameter	Hyper Red	Units		
Power dissipation	75	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	185	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3 Seconds			
Lead Solder Temperature [3]	260°C For 5 Seconds			

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAJ2818 **REV NO: V.1** DATE: APR/07/2009 PAGE: 2 OF 4 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Ting.Li ERP: 1101025550


Kingbright





RELATIVE INTENSITY Vs. WAVELENGTH


Hyper Red


L-9294SURCK












SPEC NO: DSAJ2818 **REV NO: V.1** DATE: APR/07/2009 PAGE: 3 OF 4 APPROVED: WYNEC **CHECKED: Allen Liu** ERP: 1101025550 DRAWN: Ting.Li

Kingbright



SPEC NO: DSAJ2818 APPROVED: WYNEC REV NO: V.1 CHECKED: Allen Liu DATE: APR/07/2009 DRAWN: Ting.Li PAGE: 4 OF 4 ERP: 1101025550