

L-57EGW

HIGH EFFICIENCY RED GREEN

PAGE: 1 OF 3

Features


- •LOW POWER CONSUMPTION.
- •I.C. COMPATIBLE.
- •LONG LIFE SOLID STATE RELIABILITY.
- •RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made With Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.
- Lead spacing is measured where the leads emerge from the package.
 Specifications are subject to change without notice.

SPEC NO: DSAA4040 **REV NO: V.7** DATE: MAR/24/2005 APPROVED: J. Lu CHECKED: Allen Liu DRAWN: Y.W.WANG

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) @ 20mA		Viewing Angle
		,,	Min.	Тур.	2 0 1/2
L-57EGW	HIGH EFFICIENCY RED (GaAsP/GaP)	WHITE DIFFUSED	10	30	60°
	GREEN (GaP)	WHITE DIFFUSED	10	20	

Note

Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red Green	627 565		nm I _F =20mA	
λD	Dominant Wavelength	High Efficiency Red Green	625 568		nm	I _F =20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red Green	45 30		nm	I _F =20mA
С	Capacitance	High Efficiency Red Green	15 15		pF	V _F =0V;f=1MHz
V _F	Forward Voltage	High Efficiency Red Green	2.0 2.2	2.5 2.5	V	I _F =20mA

Absolute Maximum Ratings at TA=25°C

Parameter	High Efficiency Red	Green	Units			
Power dissipation	105	105	mW			
DC Forward Current	30	25	mA			
Peak Forward Current [1]	160	140	mA			
Operating / storage Temperature	-40°C To +85°C					
Lead Solder Temperature [2]	260°C For 3 Seconds					
Lead Solder Temperature [3]	260°C For 5 Seconds					


Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAA4040 REV NO: V.7 DATE: MAR/24/2005 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: Y.W.WANG


 $^{1.\}theta1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright





High Efficiency Red /Green


L-57EGW











Remarks:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

- 1. Wavelength: +/-1nm
- 2. Luminous Intensity: +/-15%
- 3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAA4040 REV NO: V.7 DATE: MAR/24/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: Y.W.WANG