

M 620, Platinum Resistance Temperature Detector according to DIN EN 60751

Temperature range -70 °C to +500 °C, short-term up to +550 °C

M series PRTDs are designed for large volume applications where long-term stability, interchangeability and accuracy over a large temperature range are vital. Due to the high resistance values of 2000 Ω the signal gain is excellent.

Typical applications are found in Automotive, White goods, HVAC, Medical and Industrial equipment.

Nominal Resistance R0	Tolerance	Order Number
	DIN EN 60751 2009-05	Plastic Bag
2000 Ohm at 0 °C	F 0.3 (Class B)	32 208 541

The measuring point for the nominal resistance is defined at 8 mm from the end of the sensor body.

Temperature and tolerance range

-70 °C to +500 °C (continuous operation)
(temporary use to +550 °C possible)
Tolerance class F 0.3 (B): -70 °C to +500 °C

Temperature coefficient

TCR = 3850 ppm/K

Response time

Water current (v= 0.4m/s): t0.5 = 0.08 s
t0.9 = 0.25 s
Air stream (v= 2m/s): t0.5 = 3.7 s
t0.9 = 11.5 s

Measuring current


2000 Ω: 0.1 to 0.3 mA
(self-heating has to be considered)

Long-term stability

R0-Drift 0.04 % after 1000 hours at 500 °C

Self-heating

0.3 K/mW at 0 °C



Insulation resistance

> 100 MΩ at 20 °C
> 2 MΩ at 500 °C

Vibration resistance

At least 40 g acceleration at 10 to 2000 Hz,
depends on installation



The information provided in this data sheet regarding the technical characteristics of the product describe the quality of the product, but shall not be qualified or construed as quality guarantees (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product; measurements in productive use may vary significantly depending on the specific conditions of use.

The customer is solely responsible to check whether the product is suited for the intended use; in this respect Heraeus cannot assume any liability. The sale of any products of Heraeus is exclusively subject to the General Terms of Sale and Delivery of Heraeus in their current version, which is available under www.heraeus.com/gtc. This data sheet is subject to changes without prior notice.

Heraeus Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany
Web: www.heraeus-nexensos.com

M 620, Platinum Resistance Temperature Detector according to DIN EN 60751 Temperature range -70 °C to +500 °C, short-term up to +550 °C

Shock resistance

At least 100g acceleration with 8ms half sine wave, depends on installation

Leads

Pt clad Ni- wire

Lead lengths (L)

10 mm ± 1 mm

Connection technology

Suitable for welding, crimping and brazing

Tensile strength of leads

≥ 9 N

Packaging

Plastic bag

Storage life

Min. 12 months (in original packaging)

Note

Other tolerances, values of resistance and wire lengths are available on request.

California Proposition 65



WARNING:

This product can expose you to chemicals including lead oxide, which is known to the State of California to cause cancer and birth defects or other reproductive harm, and including cobalt oxide, nickel and cobalt, which are known to the State of California to cause cancer. For more information go to www.p65warnings.ca.gov.



The information provided in this data sheet regarding the technical characteristics of the product describe the quality of the product, but shall not be qualified or construed as quality guarantees (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code.

The information provided in this data sheet regarding measurement values (response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product; measurements in productive use may vary significantly depending on the specific conditions of use.

The customer is solely responsible to check whether the product is suited for the intended use; in this respect Heraeus cannot assume any liability. The sale of any products of Heraeus is exclusively subject to the General Terms of Sale and Delivery of Heraeus in their current version, which is available under www.heraeus.com/gtc. This data sheet is subject to changes without prior notice.

Heraeus Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany
Web: www.heraeus-nexensos.com

