


MATERIAL:

Contact :
Phosphor Bronze thickness 0.15mm
Plating :
Contact Plating, Tin plated 60u"-80u"
(Lead free plating)


Insulator : PBT-4830 , UL 94V-0

SPECIFICATIONS:

Current Rating : 1A
Dielectric withstanding Voltage : 1000v RMS/minute
Insulator resistance : 5000 Megohms min.
Contact resistance : 20 milliohms initial
30 milliohms after test.
Operating temperatures : -55°c to 85°c
Insertion force : 340g(12 oz) max.per contact.
Withdrawal force : 80g(2.82 oz) min.per contact



CKT	A±0.20	B±0.20
08	10.16	7.62



PCB LAYOUT

RoHS compliant

Unit: mm

Scale	Free						Date	Name	Customer-No.
TOLERANCE						Drawn	20.07.2012	Lucas	CONRAD 183799
X.	±X					Approved	20.07.2012	Jackey	ASSMANN WSW-No.
X.X	±X								A 08-LC-TT
X.XX	±X								Drawing-No.
DIM	TOL								ASS 4915 CO
X.°	±X°								rev00
X.X°	±X°	©	Drawn	20.07.2012	Lucas			Replace	Sheet
Angle	TOL	Id.	Modification	Date	Name				