












Heatsinks for LEDs

<p>art. no.</p> <p>SK 46 ...</p>		
<p>art. no.</p> <p>SK 578 ...</p>		
<p>art. no.</p> <p>SK 577 ...</p>		
<p>art. no.</p> <p>SK 569 ...</p>		
<p>art. no.</p> <p>SK 570 ...</p>		
<p>please indicate: ... </p> <p style="text-align: center;">10 15 20 25 37.5 50 1000 mm</p>		

special design, surfaces and modification to customer specification on request
surface: black anodised

Pin heatsinks Ø
 Heatsinks for LED Ø
 Special heatsink design
 Thermal conductive paste

→ B 26 - 28 Thermal conduct. foil WLFT 404/405
 → B 29 - 33 Thermally conductive material
 → A 135 - 136 SMD-heatsinks
 → E 13 Technical annotations

→ E 5
 → E 15
 → B 38 - 40
 → A 2 - 7

B 34

A

B

C

D

E

F

G

H

I

K

L

M

N