SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER :

MOTOR TYPE : MAGLE Fan & Blow

DESCRIPTION : MagLev Motor Fan

DIMENSIONS : 40X40X20 mm

MODEL: MB40200V2-0000-A99

SUNON SPEC. NO. : D04072620G-00

CUSTOMER .

APPROVAL NO.

APPROVED BY

CUSTOMER

(AUTHORIZED)

DRAWN	Anna 12/24	СНЕСКЕВ	Kiddy Cindy	APPROVED	Jacky	SPEC.NO	D04072620G-00
						ISSUE DATE	12.04.2009
						EDITION	1
						REVISION DATE	12.24.2010
						E.SPEC	E10900296

建準電機工業股份有限公司

SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.

NO. 30, LN. 296, XINYA RD., QIANZHEN DIST., TEL:886-7-8135888


KAOHSIUNG CITY 80673, TAIWAN (R.O.C) FAX:886-7-8230505/8230606/8231010

URL:http://www.sunon.com E-mail: sunon@email.sunon.com.tw

建準電機 SUNONWEALTH Page 1 of 14



I. MODEL NUMBERING SYSTEM



建準電機 SUNONWEALTH Page 2 of 14



II. SPECIFICATION

1. MECHANICAL CHARACTERISTIC

MOTOR DESIGN	2 phases, 4-poles Brushless DC motor
BEARING SYSTEM	Vapo bearing system
DIMENSIONS	See Page 6
MATERIALS OF FRAME	Thermoplastic PBT of UL 94V-0
MATERIALS OF FAN BLADE	Thermoplastic PBT of UL 94V-0
DIRECTION OF ROTATION	Counter-clockwise viewed from front of fan blade
MOUNTING HOLES	Diameter 4.3 mm in 4 holes
WEIGHT	30 g

2. ELECTRIC CHARACTERISTIC

RATED VOLTAGE	5 VDC
RATED CURRENT	123 mA / Max. 142 mA
RATED POWER CONSUMPTION	0.62 WATTS / Max. 0.71 WATTS
OPERATING VOLTAGE RANGE	3.5~6 VDC
STARTING VOLTAGE	3.5 VDC (25 deg. C POWER ON/OFF)
OPERATING TEMPERATURE RANGE	-10 to + 70 deg. C
STORAGE TEMPERATURE RANGE	-40 to + 70 deg. C





3. PERFORMANCE CHARACTERISTIC

AIR FLOW STATIC PRESSURE 0.16 Inch-H ₂ O ACOUSTIC NOISE 21 dB(A) AIR FLOW V.S. PRESSURE INSULATION CLASS UL Class A INSULATION RESISTANCE PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu PROTECTION ALL Class A UL Class A 500M ohm at 500 VDC between integer of the seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu Automatic Restart Note: In a situation where the fan is force while the electricity is on, an	
ACOUSTIC NOISE 21 dB(A) AIR FLOW V.S. PRESSURE See Page 5 INSULATION CLASS UL Class A INSULATION RESISTANCE PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu PROTECTION ACOUSTIC NOISE 21 dB(A) See Page 5 UL Class A 500M ohm at 500 VDC between integer of the seconds wire (+) Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu Automatic Restart Note: In a situation where the fan is force while the electricity is on, an	
AIR FLOW V.S. PRESSURE See Page 5 UL Class A INSULATION RESISTANCE PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY PROTECTION AIR FLOW V.S. PRESSURE See Page 5 UL Class A 500M ohm at 500 VDC between interest of lead wire (+) Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu Automatic Restart Note: In a situation where the fan is force while the electricity is on, an	
INSULATION CLASS UL Class A INSULATION RESISTANCE PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY PROTECTION Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY Mutomatic Restart Note: In a situation where the fan is force while the electricity is on, an	
INSULATION RESISTANCE PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY PROTECTION Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY Matterial Restart Note: In a situation where the fan is force while the electricity is on, an	
PLASTIC HOUSING DIELECTRIC STRENGTH Applied AC 500 V for one minute of Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu PROTECTION Matternatic Restart Note: In a situation where the fan is force while the electricity is on, an	
Seconds between housing and lead LIFE EXPECTANCY 60,000 Hours at 40 deg. C, 65% hu PROTECTION Mutomatic Restart Note: In a situation where the fan is force while the electricity is on, an	nal stator and
PROTECTION Automatic Restart Note: In a situation where the fan is force while the electricity is on, an	
Note: In a situation where the fan is force while the electricity is on, an	nidity, 90% CL.
temperature will be prevented by te electrical power to the motor. The frestart when the locked rotor conditions are proportion.	ncrease in coil nporarily turning off the

4. SAFETY


SAFETY	UL	CUR	TUV
NO.	E77551	E77551	✓



MODEL: MB40200V2-0000-A99


PERFORMANCE CURVES

STATIC PRESSURE



建準電機 SUNONWEALTH Page 5 of 14





建準電機 SUNONWEALTH Page 6 of 14



LABEL BLACK WORD **Q** SUNON COLOR:SILVER **BLACK WORD** MagLev **COLOR:PANTONE 347C** MB40200V2-0000-A99 GREEN-**BLACK WORD** COLOR:SILVER DC5V ____ 0.62W Type of Electronically Protected (DC FAN only) MADE IN Printing Plant Code By Manufacture plant:CHINA **TAIWAN** DATE CODE





III. OTHER SPECIFIED TESTING

The following is a general description of certain tests that are performed on representative Sunon fans. Nothing in this document is intended to suggest that these tests are performed on every model of Sunon fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this Section, Sunon can provide such an explanation upon request.

1. DROP PROOF TEST

Fans are packaged in a standard size shipping box and are dropped to the ground from certain heights and angles depending on the weight of the particular box.

2. HUMIDITY PROOF TEST

The fan is operated for 96 continuous hours in an environment with humidity of 90% to 95% RH at $60^{\circ}\text{C} \pm 2^{\circ}\text{C}$.

3. VIBRATION PROOF TEST

Vibration with an amplitude 2mm and a frequency of 5-55-5hz is applied in all 3 directions (X,Y,Z), in cycles of 1 hour each, for a total vibration time of 3hours.

4. THERMAL CYCLING TEST

The fan is operated in a testing chamber for 50 cycles. In each cycle, the temperature is gradually increased from -10°C to 70°C for 90 minutes, and subsequently operated at 70°C for 120 minutes. The temperature is then gradually decreased from 70°C to -10°C for 90 minutes, and subsequently operated at -10°C for 120 minutes.

5. SHOCK PROOF TEST

100G of force is applied in the 3 directions (X,Y, and Z) for 2 milliseconds each.

6. LIFE EXPECTANCY

The "Life Expectancy" of SUNON fans is determined in SUNON's reliability test laboratory by using temperature chambers. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

建準電機 SUNONWEALTH Page 8 of 14




IV. CHARACTERISTIC DEFINITION

The following is a general description of certain tests that are performed on representative Sunon fans in order to determine the specifications of the fan. Nothing in this document is intended to suggest that these tests are performed on every model of Sunon fan. Moreover, the descriptions that follow each test are meant only to provide a general explanation of each test. If you would like a more detailed explanation as to any test identified in this Section, Sunon can provide such an explanation upon request.

1. ACOUSTICAL NOISE

Measured in a semi-anechoic chamber with background noise level below 15dB(A).



1 METER FROM MICROPHONE TO FAN INTAKE


The fan is running in free air under shaft horizontal condition with the microphone at distance of one meter from the fan intake.

2. INPUT POWER

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

3. RATED CURRENT

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.





4. RATED SPEED

Measured after continuous 10 minute operation at rated voltage in clean air (STATIC PRESSURE=0), and at ambient temperature of 25 degrees C under shaft horizontal condition.

5. STARTING VOLTAGE

Measured the voltage which enables to start the fan in the clean air (static pressure = 0) by switching on at the voltage under shaft horizontal condition. It is not at continuously increasing voltage adjustment.

6. LOCKED ROTOR CURRENT

Measured immediately after the fan blade is locked.

7. AIR FLOW AND STATIC PRESSURE

The performance specification of air flow and static pressure shown in this specification for approval is measured using the exhaust method. A double chamber is used in accordance with AMCA 210 standard or DIN 24163 specification . The values are recorded when the fan speed has stabilized at rated voltage.

8. INSULATION RESISTANCE

- 1. PLASTIC HOUSING:
 - (1) Measured between internal stator and lead wire(+).
 - (2) Measured between housing and lead wire(+).

2. ALUMINIUM HOUSING:

Measured between internal stator and lead wire(+).

9. DIELECTRIC STRENGTH

Measure between housing and lead wire(+).

建準電機 SUNONWEALTH Page 10 of 14



V. NOTE

I.SAFETY

- 1. DO NOT use or operate this fan in excess of the limitations set forth in this specification. SUNON is not be responsible for the non-performance of this fan and/or any damages resulting from its use, if it is not used or operated in accordance with the specifications.
- 2. SUNON recommends adding a protection circuit to the product or application in which this fan is installed, such as a thermo-fuse, or current-fuse or thermo-protector. The failure to use such a device may result in smoke, fire, electric shock by insulation degradation in cases of motor lead short circuit, overload, or over voltage, and/or other failure.
- 3. SUNON recommends installing a protection device to the product or application in which this fan is installed if there is a possibility of reverse-connection between VDC (+) and GND (-). The failure to install such a device may result in smoke, fire, and/or destruction, although these conditions may not manifest immediately.
- 4. This fan must be installed and used in compliance with all applicable safety standards and regulations.
- 5. Use proper care when handling and/or installing this fan. Improper handling or installation of this fan may cause damage that could result in unsafe conditions.
- 6. Use proper care during installation and/or wiring. Failure to use proper care may cause damage to certain components of the fan including, but not limited to, the coil and lead wires, which could result in smoke and/or fire.
- 7. DO NOT use power or ground PWM to control the fan speed. If the fan speed needs to be adjusted, please contact Sunon to customize the product design for your application.
- 8. For critical or extreme environments, including non stop operation, please contact Sunon and we will gladly provide assistance with your product selection to ensure an appropriate cooling product for your application.

建準電機 SUNONWEALTH Page 11 of 14



II. SPECIFICATION MODIFICATION

- 1. SUNON offers engineering assistance on fan installation and cooling system design.
- 2. All changes, modifications and/or revisions to the specifications, if any, are incorporated in the attached specifications.
- 3. No changes, modifications and/or revisions to these specifications are effective absent agreement, by both Sunon and the customer, in writing.
- 4. This fan will be shipped in accordance with the attached specification unless SUNON and the customer have agreed otherwise, in writing, as specificied in Paragraph 3, above.

III. OTHER

- 1. When building your device, please examine thoroughly any variation of EMC, temperature rise, life data, quality, etc. of this product by shock/drop/vibration testing, etc. If there are any problems or accidents in connection with this product, it should be mutually discussed and examined.
- 2. Use proper care when handling this fan. Components such as fan holders or bearings may be damaged, if touched with fingers or other objects. Additionally, static electricity (ESD) may damage the internal circuits of the fan.
- 3. DO NOT operate this fan in proximity to hazardous materials such as organic silicon, cyanogens, formalin, phenol, or corrosive gas environments including, but not limited to, H₂S, SO₂, NO₂, or Cl₂.
- 4. SUNON recommends that you protect this fan from exposure to outside elements such as dust, condensation, humidity or insects. Exposure of this fan to outside elements such as dust, condensation, humidity or insects may affect its performance and may cause safety hazards. SUNON does not warrant against damage to the product caused by outside elements.
- 5. This fan must be installed properly and securely. Improper mounting may cause harsh resonance, vibration, and noise.

建準電機 SUNONWEALTH Page 12 of 14



- 6. Fan guards may prevent injury during handling or installation of the fan and are available for sale with this fan.
- 7. Unless otherwise noted, all testing of this fan is conducted at 25°C ambient temperature and sixty-five percent (65%) relative humidity.
- 8. DO NOT store this fan in an environment with high humidity. This fan must be stored in accordance with the attached specifications regarding storage temperature. If this fan is stored for more than 6 months, SUNON recommends functional testing before using.
- 9. SUNON reserves the right to use components from multiple sources at its discretion. The use of components from other sources will not affect the specifications as described herein.
- 10. The "Life Expectancy" of this fan has not been evaluated for use in combination with any end application. Therefore, the Life Expectancy Test Reports (L10 and MTTF Report) that relate to this fan are only for reference.

VI. WARRANTY

This fan is warranted against all defects which are proved to be fault in our workmanship and material for one year from the date of our delivery. The sole responsibility under the warranty shall be limited to the repair of the fan or the replacement thereof, at SUNON's sole discretion. SUNON will not be responsible for the failures of its fans due to improper handing, misuse or the failure to follow specifications or instructions for use. In the event of warranty claim, the customer shall immediately notify SUNON for verification. SUNON will not be responsible for any consequential damage to the customer's equipment as a result of any fans proven to be defective.

建準電機 SUNONWEALTH Page 13 of 14



Declaration of RoHS

Control declaration of environment-related substances/materials

1. In accordance with the Restriction of Hazardous Substances (RoHS) Directive, Sunon product have complied with law and discipline not to employ the forbidden substances, and restrict the allowable concentration of some limited substances deliberately in our components.

No		Criteria		
1	CFCs & HCFCs (ozone depleting	Forbidden		
2	Chlorinated Organic Solvent	Forbidden		
3	Lead and its compounds	Plastic (Frame, Impeller, wire harness, etc.)	<100ppm	
		Solder	<1000ppm	
		Steel alloy	<3500ppm	
		Aluminium alloy	<4000ppm	
		Copper alloy	<4wt%	
		Solder	<20ppm	
1	Cadmium and its compounds	Parts composed of metals containing zinc	<100ppm	
4		(e.g. brass, zinc for die casting)		
		Plastic	<5ppm	
5	PBBs and PBDEs	Forbidden		
6	PCB and PCT	Forbidden		
7	CP, Short-chain Chlorinated pa	Forbidden		
8	Mirex	Forbidden		
9	PCN	Forbidden		
10	Hexavalent Chromium compou	<100ppm		
11	Mercury and its compounds	Forbidden		
12	Asbestos	Forbidden		
13	Organic Tin compounds	Forbidden		
14	Azo compounds	Forbidden		
15	TBBP-A in external case plastic	<1000ppm		
16	Nickel in external case parts, whic	<1000ppm		



