




富仲企業股份有限公司

No. 79, Lane 258, Shoeh Yuan Rd., Feng Yuan, 420 Taichung, Taiwan

E-mail: taiwan.cap@msa.hinet.net

<http://www.taiwan-capacitor.com.tw>



Model: BX + RR

Capacitance (MFD)	Rated Voltage (VAC)	Size (mm), ± 1 mm			Lead wires (20AWG) ± 5 m/m	
		L	W	H	L1*R	L2*R
1.5 μ F	450 V.AC	37	15	26	Red: 85*10	Red:85*10

製品規範 (SPECIFICATION):

Standards (依據規範)	CNS 4327, JIS C4908, IEC 252		
Capacity tolerance (容量容許差)	(J) +,-5 %,		
Frequency (定額頻率)	50/60 Hz		
Insulation resistance (絕緣電阻)	Terminals to case (Above 2000 M. Ω)		
Voltage withstand (耐電壓)	Between terminals	W.V \times 1.5	One minute
	Terminals to case	W.V \times 2+1000 (min. 2000)	One minute
Dissipation factor (介質損失率)	MPP TYPE	Below 0.15%	
Range of temp (使用溫度)	VDE / -40 $^{\circ}$ C ~ +85 $^{\circ}$ C	UL /-25 $^{\circ}$ C ~ +70 $^{\circ}$ C	
Continue life test (連續耐用試驗)	W.V \times 120% 1000 \pm 12hr		
On-off life test (斷續耐用試驗)	W.V \times 140% (on 2 sec. / off 2 sec.) Test cycle100,000 \pm 1,000 times		