



MATERIAL:
 Contact : Phosphor Bronze thickness 0.15mm
 Plating : Contact Plating, Tin plated 60u"-80u" (Lead free plating)
 Insulator : PBT-4830 , UL 94V-0

SPECIFICATIONS:
 Current Rating : 1A
 Dielectric withstanding Voltage : 1000v RMS/minute
 Insulator resistance : 5000 Megohms min.
 Contact resistance : 20 milliohms initial
 30 milliohms after test.
 Operating temperatures : -55°c to 85°c
 Insertion force : 340g(12 oz) max.per contact.
 Withdrawal force : 80g(2.82 oz) min.per contact



CKT	A±0.20	B±0.20
16	20.32	17.78



PCB LAYOUT

RoHS compliant
 Unit: mm

Scale	Free				Date	Name	Customer-No.
TOLERANCE					Drawn	Lucas	CONRAD 183803
X.	±X				Approved	Jackey	ASSMANN WSW-No.
X.X	±X						A 16-LC-TT
X.XX	±X						Drawing-No.
DIM	TOL						ASS 4917 CO
X.°	±X°						rev00
X.X°	±X°	©	Drawn	20.07.2012	Lucas		
Angle	TOL	Id.	Modification	Date	Name		