


SPECIFICATION

Current Rate:1 AMP
 Insulation Resistance:1000M Ω Min
 Contact Resistance:30m Ω Max
 Dielectric voltage:600V AC for one minute
 Operation Temperature:-50°C to +105°C
 Soldering Temperature:200°C / 5 Sec

MATERIAL


Insulator:Hi-temp PBT. UL 94V-0
 Contact material:Phorphos Bronze Jis 5210
 contact Platred:150U" tin over 40U" nickel






Recommended PCB Layout
 (PCB TOLERANCE ±0.05)

No. of contact	A±0.15	B±0.15	C±0.1	D±0.1	E±0.1	F±0.1
20	15.50	15.50	5.08	5.08	5.08	5.08
28	18.04	18.04	7.62	7.62	7.62	7.62
32	18.04	20.60	7.62	10.16	7.62	10.16
44	23.48	23.48	12.70	12.70	12.70	12.70
52	25.88	25.88	15.24	15.24	15.24	15.24
68	31.66	31.66	20.32	20.32	20.32	20.32
84	36.66	36.66	25.40	25.40	25.40	25.40

ORDER INFORMATION



©:Standard Recommend



品名 TITLE	PLCC SOCKET THROUGH HOLE TYPE				
品號 PART NO.	DPLCC-XX-L			日期 DATE	08/08/2005
圖號 DRAWING NO.	DPLCC-XX-L	版本 REV.	B	繪圖 DRAWN	Kent
客戶品號 CUSTOMER P/N		比例 SCALE	FREE	核對 CHECKED	Paul
公差 TOLERANCE	.X ±0.3 .XX ±0.25	單位 UNIT	mm	核准 APPROVED	James

AREA	REV.	DESCRIPTION	DATE