












## Heatsinks for LEDs

<b>art. no.</b>          <b>SK 46 ...</b>		
<b>art. no.</b>          <b>SK 578 ...</b>		
<b>art. no.</b>          <b>SK 577 ...</b>		
<b>art. no.</b>          <b>SK 569 ...</b>		
<b>art. no.</b>          <b>SK 570 ...</b>		
<b>please indicate:</b> ...  <b>10 15 20 25 37.5 50 1000 mm</b>		

special design, surfaces and modification to customer specification on request

**surface:** black anodised

Pin heatsinks Ø  
Heatsinks for LED Ø  
Special heatsink design  
Thermal conductive paste

→ B 26 - 28 Thermal conduct. foil WLFT 404/405  
→ B 29 - 33 Thermally conductive material  
→ A 135 - 136 SMD-heatsinks  
→ E 13 Technical annotations

→ E 5  
→ E 15  
→ B 38 - 40  
→ A 2 - 7

**B 34**

A

B

C

D

E

F

G

H

I

K

L

M

N