












## Heatsinks for LEDs

<p>art. no.</p> <p><b>SK 46 ...</b></p>		
<p>art. no.</p> <p><b>SK 578 ...</b></p>		
<p>art. no.</p> <p><b>SK 577 ...</b></p>		
<p>art. no.</p> <p><b>SK 569 ...</b></p>		
<p>art. no.</p> <p><b>SK 570 ...</b></p>		
<p>please indicate: ... </p> <p style="text-align: center;"><b>10 15 20 25 37.5 50 1000 mm</b></p>		

special design, surfaces and modification to customer specification on request  
**surface:** black anodised

Pin heatsinks Ø  
 Heatsinks for LED Ø  
 Special heatsink design  
 Thermal conductive paste

→ B 26 - 28 Thermal conduct. foil WLFT 404/405  
 → B 29 - 33 Thermally conductive material  
 → A 135 - 136 SMD-heatsinks  
 → E 13 Technical annotations

→ E 5  
 → E 15  
 → B 38 - 40  
 → A 2 - 7

**B 34**

A

B

C

D

E

F

G

H

I

K

L

M

N