




- Ground

Power

LED

Internal Pin

SWD Pin
- Digital Pin

Analog Pin

Other Pin

Microcontroller's Port

Default

⚠


MAXIMUM current per I/O pin is 20mA

⚠

MAXIMUM current per +3.3V pin is 50mA

VIN

6-20 V input to the board.




- Ground
- Power
- LED
- Internal Pin
- SWD Pin
- Digital Pin
- Analog Pin
- Other Pin
- Microcontroller's Port
- Default
- Analog
- Communication
- Timer
- Interrupt
- Sercom


MAXIMUM current per I/O pin is 20mA

MAXIMUM current per +3.3V pin is 50mA

VIN 6-20 V input to the board.



Digital pins D22-D53



- Ground
- Power
- LED
- Internal Pin
- SWD Pin
- Digital Pin
- Analog Pin
- Other Pin
- Microcontroller's Port
- Default
- Analog
- Communication
- Timer
- Interrupt
- Sercom


MAXIMUM current per I/O pin is 20mA

MAXIMUM current per +3.3V pin is 50mA

VIN 6-20 V input to the board.

NOTE: CIPO/COPI have previously been referred to as MISO/MOSI





VIN 6-20 V input to the board.

NOTE: CIPO/COPI have previously been referred to as MISO/MOSI

Last update: 16/12/2020

