

# Thermoelectric module QC- 35-1.4-3.7

## Perfomance Data


I <sub>max</sub> (amps)	4	$\Delta T = \Delta T_{max}$ . Th=25 ± 0.5 °C.
V <sub>max</sub> (volts)	4	Th=25 ± 0.5 °C. $\Delta T = \Delta T_{max}$ . I=I <sub>max</sub> ± 0.1A
ΔT <sub>max</sub> (°C)	71	Th=25 ± 0.5 °C. I=I <sub>max</sub> ± 0.1A
Q <sub>max</sub> (watts)	9.6	Th=Tc=25 ± 0.5 °C. I=I <sub>max</sub> ± 0.1A
AC resistance (ohms)	0.9	25 ± 0.5 °C.

Environment: dry air, N<sub>2</sub>

Tolerances for thermal and electrical parameters ± 10%

Drawing № ND 038.00.00


Dimensions in millimeters



## Options

Model Number	Description
TM-35-1.4-3.7 M	High reliable version on Cold Side



Lead wire insulation	Module maximum processing temperature
PVC	90°C
Silicone	200°C
PTFE	200°C



## Additional

- RoHS 2002/95/EC compliant
- Cold Side and Hot Side Ceramics: Al<sub>2</sub>O<sub>3</sub>, white 96%
- Assembling Solder: SnSb, M.P. 232 °C ; SnCu M.P. 227 °C

Performance graphs for QC-35-1.4-3.7 modules at Th=25 °C  
 Environment: dry air, N<sub>2</sub>





$Q_c$  -refrigerating capacity at cold side of the module (Watts),

$\Delta T=T_{c-Th}$  - temperature difference between cold and hot sides of the module (°C),

$I$  - DC current through the modules (Amps)

$V$  -voltage applied to the module (Volts).

Performance graphs for QC-35-1.4-3.7 modules at Th=50 °C  
Environment: dry air, N<sub>2</sub>



Qc -refrigerating capacity at cold side of the module (Watts),

$\Delta T=T_c-T_h$  - temperature difference between cold and hot sides of the module (°C),

I - DC current through the modules (Amps)

V -voltage applied to the module (Volts).