

Antenna cable - FL LCX PIG-EF142-N-N - 2700677

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Antenna cable as an accessory for leaky wave conductors, length: 1 m, N (male) - N (male), attenuation: approximately 0.93 dB at 2.4 GHz and 1.6 dB at 5 GHz

Key commercial data

package_quantity	1
GTIN	4046356619578

Technical data

Cable type

Cable type	EF 142
Cable, attenuation	Approx. 0.93 dB/m at 2.4 GHz

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C

External sheath

Outer sheath, material	RADOX®(LSFH)
------------------------	--------------

Mechanical properties

Bending radius, long-term	30 mm
---------------------------	-------

General

Impedance	50 Ω
Connection method	N (male)
Connection method	N (male)

classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	19070490
eCl@ss 7.0	19070490

Antenna cable - FL LCX PIG-EF142-N-N - 2700677

classifications

eCl@ss

eCl@ss 8.0	19070490
-------------------	----------

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002498

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>