

# Thermoelectric module - 35-1.4-3.7

## Performance Data


|                       |     |                                                                             |
|-----------------------|-----|-----------------------------------------------------------------------------|
| $I_{max}$ (amps)      | 4   | $\Delta T = \Delta T_{max}$ . $T_h = 25 \pm 0.5$ °C.                        |
| $V_{max}$ (volts)     | 4   | $T_h = 25 \pm 0.5$ °C. $\Delta T = \Delta T_{max}$ . $I = I_{max} \pm 0.1A$ |
| $\Delta T_{max}$ (°C) | 71  | $T_h = 25 \pm 0.5$ °C. $I = I_{max} \pm 0.1A$                               |
| $Q_{max}$ (watts)     | 9.6 | $T_h = T_c = 25 \pm 0.5$ °C. $I = I_{max} \pm 0.1A$                         |
| AC resistance (ohms)  | 0.9 | $25 \pm 0.5$ °C.                                                            |

Environment: dry air,  $N_2$

Tolerances for thermal and electrical parameters  $\pm 10\%$

Drawing № ND 038.00.00

Dimensions in millimeters




## Options

| Model Number    | Description                        |
|-----------------|------------------------------------|
| TM-35-1.4-3.7 M | High reliable version on Cold Side |

| Lead wire insulation | Module maximum processing temperature |
|----------------------|---------------------------------------|
| PVC                  | 90°C                                  |

Maximum processing temperature +170°C



## Additional

- RoHS 2002/95/EC compliant
- Cold Side and Hot Side Ceramics:  $Al_2O_3$ , white 96%
- Assembling Solder: SnSb, M.P. 232 °C ; SnCu M.P. 227 °C