

Inline terminal - IB IL DOR LV-SET-PAC - 2861645

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Inline distance terminal, complete with accessories

Product Description

The Inline distance terminals have been designed for use within an Inline station. Within an Inline station, a relay terminal can be used to switch voltages that are not available in the segment in which the terminal is located (e.g. switching 230 V AC within a 24 V DC segment). In this case, place a distance terminal before and after the relay terminal block. Doing so maintains the isolating distance between the individual areas. The distance terminals interrupt the potential jumpers for the main voltage, segment voltage, ground, and functional earth ground. Lines are not connected to these terminals.

Key commercial data

package_quantity	1
GTIN	4017918894481

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
--------------------------------	---

Dimensions

Width	24.4 mm
Height	119.8 mm
Depth	71.5 mm

Interfaces

Connection method	Inline data jumper
Interface	Inline local bus

General

Weight	32 g
---------------	------

classifications

eCl@ss

eCl@ss 4.0	27250308
eCl@ss 4.1	27250281
eCl@ss 5.0	27250304
eCl@ss 5.1	27242610

Inline terminal - IB IL DOR LV-SET-PAC - 2861645

classifications

eCl@ss

eCl@ss 6.0	27242610
eCl@ss 7.0	27242610
eCl@ss 8.0	27242610

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC001600
ETIM 4.0	EC001600
ETIM 5.0	EC001600






UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

approvals

UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / ABS / GL-SW / BSH / UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / ABS / GL-SW / BSH / cULus Recognized / GL /

Approval details



Inline terminal - IB IL DOR LV-SET-PAC - 2861645

approvals


DNV

ABS

GL-SW

BSH

UL Recognized 

cUL Recognized 



LR

GL

BV

DNV

GL-SW

BSH

cULus Recognized  US

Inline terminal - IB IL DOR LV-SET-PAC - 2861645

accessories


Terminal marking

ESL 62X10 - 0809492




Drawings

Connection diagram



Inline terminal - IB IL DOR LV-SET-PAC - 2861645

Dimensioned drawing



Schematic diagram

